MOSFET - Power, Single P-Channel, SOT-23 -50 V, 10 Ω

BSS84L, BVSS84L, SBSS84L

- SOT-23 Surface Mount Package Saves Board Space
- BV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Rating	Symbol	Value	Unit
Drain-to-Source Voltage	V_{DSS}	-50	Vdc
Gate-to-Source Voltage - Continuous	V _{GS}	± 20	Vdc
Drain Current Continuous @ $T_A = 25^{\circ}C$ Pulsed Drain Current ($t_p \le 10 \mu s$)	I _D I _{DM}	-130 -520	mA
Total Power Dissipation @ T _A = 25°C	P_{D}	225	mW
Operating and Storage Temperature Range	T _J , T _{stg}	– 55 to 150	°C
Thermal Resistance - Junction-to-Ambient	$R_{\theta JA}$	556	°C/W
Thermal Resistance – Junction-to-Ambient (Note 1)	$R_{\theta JA}$	377.2	°C/W
Maximum Lead Temperature for Soldering Purposes, for 10 seconds	TL	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


1. R_{θ,JA} is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. And the R_{θ,JA} is determined by the user's board design. The maximum rating presented here is based on mounting the part on JEDEC Standard 51-3/51-7.



ON Semiconductor®

www.onsemi.com


V _{(BR)DSS}	R _{DS(ON)} MAX
–50 V	10 Ω @ -10 V





SOT-23 CASE 318 STYLE 21

MARKING DIAGRAM & PIN ASSIGNMENT



PD = Specific Device Code

M = Date Code ■ = Pb-Free Package

(*Note: Microdot may be in either location)

ORDERING INFORMATION

Device	Package	Shipping [†]
BSS84LT1G, BVSS84LT1G, SBSS84LT1G	SOT-23 (Pb-Free)	3,000 / Tape & Reel
BSS84LT7G	SOT-23 (Pb-Free)	3,500 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

BSS84L, BVSS84L, SBSS84L

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

С	Symbol	Min	Тур	Max	Unit	
OFF CHARACTERISTICS				•	•	•
Drain-to-Source Breakdown Volt (V _{GS} = 0 Vdc, I _D = -250 μAdc		V _{(BR)DSS}	-50	-	-	Vdc
Zero Gate Voltage Drain Current			- - -	- - -	-0.1 -15 -60	μAdc
Gate-Body Leakage Current (V _G	$_{\rm S}$ = \pm 20 Vdc, V _{DS} = 0 Vdc)	I _{GSS}	-	-	±10	nAdc
ON CHARACTERISTICS (Note 2)					
Gate-Source Threaded Voltage (V _{DS} = V _{GS} , I _D = -250 μA)	V _{GS(th)}	-0.9	-	-2.0	Vdc
Static Drain-to-Source On-Resis	R _{DS(on)}	-	4.7	10	Ω	
Transfer Admittance (V _{DS} = −25 \	y _{fs}	50	-	_	mS	
DYNAMIC CHARACTERISTICS						
Input Capacitance	V _{DS} = 5.0 Vdc	C _{iss}	-	36	-	pF
Output Capacitance	V _{DS} = 5.0 Vdc	C _{oss}	-	17	-	
Transfer Capacitance	V _{DG} = 5.0 Vdc	C _{rss}	_	6.5	_	
SWITCHING CHARACTERISTIC	S (Note 3)					
Turn-On Delay Time		t _{d(on)}	-	3.6	-	ns
Rise Time	$V_{DD} = -15 \text{ Vdc}, I_D = -2.5 \text{ Adc},$	t _r	-	9.7	-	
Turn-Off Delay Time	$R_L = 50 \Omega$	t _{d(off)}	-	12	-	
Fall Time		t _f	-	1.7	-	
Gate Charge	$V_{DD} = -40 \text{ Vdc}, I_D = -0.5 \text{ A}, V_{GS} = -10 \text{ V}$	Q _T	_	2.2	-	nC
SOURCE-DRAIN DIODE CHAR	ACTERISTICS	•		-	-	-
Continuous Current		IS	-	_	-0.130	Α
Pulsed Current		I _{SM}	-	_	-0.520	
Forward Voltage (Note 3)	$V_{GS} = 0 \text{ V, } I_{S} = -130 \text{ mA}$	V _{SD}	-	_	-2.2	V

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

- 2. Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≤ 2%.
- 3. Switching characteristics are independent of operating junction temperature.

TYPICAL ELECTRICAL CHARACTERISTICS




Figure 1. Transfer Characteristics




Figure 2. On-Region Characteristics

BSS84L, BVSS84L, SBSS84L

TYPICAL ELECTRICAL CHARACTERISTICS




Figure 3. On-Resistance versus Drain Current

Figure 4. On-Resistance versus Drain Current




Figure 5. On-Resistance Variation with Temperature

Figure 6. Gate Charge




Figure 7. Body Diode Forward Voltage



SOT-23 (TO-236) CASE 318-08 **ISSUE AS**

DATE 30 JAN 2018

SCALE 4:1 D - 3X b

TOP VIEW







RECOMMENDED SOLDERING FOOTPRINT



DIMENSIONS: MILLIMETERS

NOTES:

- NOTES:
 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
 2. CONTROLLING DIMENSION: MILLIMETERS.
 3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH.
 MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF THE BASE MATERIAL
- 4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH,

	PROT	RUSIONS, OR GATE BURRS.	
--	------	-------------------------	--

	MILLIMETERS				INCHES	
DIM	MIN	NOM	MAX	MIN	NOM	MAX
Α	0.89	1.00	1.11	0.035	0.039	0.044
A1	0.01	0.06	0.10	0.000	0.002	0.004
b	0.37	0.44	0.50	0.015	0.017	0.020
С	0.08	0.14	0.20	0.003	0.006	0.008
D	2.80	2.90	3.04	0.110	0.114	0.120
E	1.20	1.30	1.40	0.047	0.051	0.055
е	1.78	1.90	2.04	0.070	0.075	0.080
L	0.30	0.43	0.55	0.012	0.017	0.022
L1	0.35	0.54	0.69	0.014	0.021	0.027
HE	2.10	2.40	2.64	0.083	0.094	0.104
Т	0°		10°	0°		10°

GENERIC MARKING DIAGRAM*



XXX = Specific Device Code

= Date Code

= Pb-Free Package

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ■", may or may not be present.

STYLE 1 THRU 5: CANCELLED	STYLE 6: PIN 1. BASE 2. EMITTER 3. COLLECTOR	STYLE 7: PIN 1. EMITTER 2. BASE 3. COLLECTOR	STYLE 8: PIN 1. ANODE 2. NO CONNECTION 3. CATHODE
OT (1 F O			

SOT-23 (TO-236)

STYLE 9:	STYLE 10:	STYLE 11:	STYLE 12:	STYLE 13:	STYLE 14:
PIN 1. ANODE	PIN 1. DRAIN	PIN 1. ANODE	PIN 1. CATHODE	PIN 1. SOURCE	PIN 1. CATHODE
ANODE	SOURCE	CATHODE	CATHODE	2. DRAIN	2. GATE
CATHODE	3. GATE	CATHODE-ANODE	ANODE	3. GATE	ANODE

STYLE 15:	STYLE 16:	STYLE 17:	STYLE 18:	STYLE 19:	STYLE 20:
PIN 1. GATE	PIN 1. ANODE	PIN 1. NO CONNECTION	PIN 1. NO CONNECTION	PIN 1. CATHODE	PIN 1. CATHODE
CATHODE	CATHODE	2. ANODE	CATHODE	2. ANODE	ANODE
ANODE	CATHODE	CATHODE	ANODE	CATHODE-ANOD	E 3. GATE

STYLE 21:	STYLE 22:	STYLE 23:	STYLE 24:	STYLE 25:	STYLE 26:
PIN 1. GATE	PIN 1. RETURN	PIN 1. ANODE	PIN 1. GATE	PIN 1. ANODE	PIN 1. CATHODE
SOURCE	OUTPUT	2. ANODE	2. DRAIN	2. CATHODE	2. ANODE
3 DRAIN	3 INPLIT	3 CATHODE	3. SOURCE	3. GATE	NO CONNECTION

STYLE 27: PIN 1. CATHODE 2. CATHODE 3. CATHODE	STYLE 28: PIN 1. ANODE 2. ANODE 3. ANODE	
DOCUMENT N	UMBER: 98ASB42226B	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red

ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

DESCRIPTION:

PAGE 1 OF 1

ON Semiconductor and the are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor and see no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative