

**DISPLAY Elektronik GmbH**

**DATA SHEET**

**BACKLIGHT**

**DE LP-507-Y**

*Product Specification*

*Version: 1*

17.11.2016

# GENERAL SPECIFICATION

---

MODEL NO. :

**DE LP-507-Y**

CUSTOMER P/N

Version No.	Change Description	Date
0	Original Version	12.10.2016
1	Change Brightness	17.11.2016

PREPARED BY: ZX

DATE: 17.11.2016

APPROVED BY: MH

DATE: 17.11.2016

**CONTENTS**

**1. FEATURES .....2**

**2. EXTERNAL DIMENSION (UNIT: MM).....2**

**3. ELECTRICAL/OPTICAL SPECIFICATIONS.....3**

**4. ACCEPT QUALITY LEVEL (AQL). ..... FEHLER! TEXTMARKE NICHT DEFINIERT.**


**5. RELIABILITY TEST..... FEHLER! TEXTMARKE NICHT DEFINIERT.**

**1. FEATURES**

Backlight Color: Yellow-Green

RoHS: Conformed

**2. EXTERNAL DIMENSION (unit: mm)**



**3. ELECTRICAL/OPTICAL SPECIFICATIONS**

## ELECTRICAL–OPTICAL CHARACTERISTICS

Ta=25°C. Unless specified, The Ambient temperature Ta=25°C

Item	Symbol	min.	typ.	max.	Unit	Condition
Forward Voltage	Vf	1.8	2.1	2.5	V	If= 20*2 mA
Power Dissipation	Pd			100	mW	If= 20*2 mA
Luminous Uniformity	$\Delta Lv$	70			%	MIN/MAX*100%
Luminance	Lv	10	35		cd/m <sup>2</sup>	If=20*2 mA T=25°C
Dominant Wave Length	$\lambda D$	565	570	575	nm	
Lifetime	50000(brightness reduce half)				Hours	

**4. ACCEPT QUALITY LEVEL (AQL).**

4.1. AQL standard value: Critical defect =0, Major defect=0.65; Minor defect =2.5.

4.2. Inspection Plan: ANSI Z-1.4, Normal Inspection Level II, Single Sampling Plan.

**5. RELIABILITY TEST**

Test Item	Test Condition
High Temperature Storage	+90°C x 96h
Low temperature Storage	-40°C x 96h
High Temperature Operation	+70°C x 96h
Low Temperature Operation	-20°C x 96h
High Temperature, High Humidity	60°C x 90%RH x 4 Weeks
Thermal Shock	-20°C x 30min → 25°C x 10s → +70°C x 30min x 5 Cycles
Vibration Test	Frequency x Swing x Time 40Hz x 4mm x 4h
Drop Test	Height x Number of drop 1.0m x 6 drops