

DISPLAY Elektronik GmbH

DATA SHEET

BACKLIGHT

DE LP-501-A

Product Specification

Version: 1

29.08.2016

CONTENTS

1. FEATURES2

2. EXTERNAL DIMENSION (UNIT: MM).....2

3. ELECTRICAL/OPTICAL SPECIFICATIONS.....3

4. ACCEPT QUALITY LEVEL (AQL).3

5. RELIABILITY TEST.....3

3. ELECTRICAL/OPTICAL SPECIFICATIONS

ELECTRICAL-OPTICAL CHARACTERISTICS

Ta=25° C. Unless specified, The Ambient temperature Ta=25° C

Item	Symbol	min.	typ.	max.	Unit	Condition
Forward Voltage	Vf	1.6	2	2.5	V	If= 30 mA
Power Dissipation	Pd			75	mW	If= 30 mA
Luminous Uniformity	ΔLv	70			%	MIN/MAX*100%
Luminance	Lv	150	300		cd/m ²	If=30 mA T=25° C
Dominant Wave Length	λD	585	-	595	nm	
Lifetime	50000 (brightness reduce half)				Hours	

4. ACCEPT QUALITY LEVEL (AQL).

4.1. AQL standard value: Critical defect =0, Major defect=0.65; Minor defect =2.5.

4.2. Inspection Plan: ANSI Z-1.4, Normal Inspection Level II, Single Sampling Plan.

5. RELIABILITY TEST

Test Item	Test Condition
High Temperature Storage	+90°C x 96h
Low temperature Storage	-40°C x 96h
High Temperature Operation	+70°C x 96h
Low Temperature Operation	-20°C x 96h
High Temperature, High Humidity	60°C x 90%RH x 4 Weeks
Thermal Shock	-20°C x 30min → 25°C x 10s → +70°C x 30min x 5 Cycles
Vibration Test	Frequency x Swing x Time 40Hz x 4mm x 4h
Drop Test	Height x Number of drop 1.0m x 6 drops