

WIZARD C2 PRO SAND



WIZARD C2 PRO SAND



SPECIFICATIONS

		Wizard C2 Pro (White)
Optics		TIR
Light output		2500 lm
Beam distance		131 m
Hotspot : Spill		70°:120°
Brightness stabilization type		Full
Number of modes		6 simple operation by default / 12 advanced operation
Modes / Runtimes	Turbo3	2500 lm / 2 h 40 min (650 lm after 30 sec)
	Turbo2	1750 lm / 2 h 45 min (650 lm after 2 min)
	Turbo1	870 lm / 2 h 50 min (650 lm after 9 min)
	Main3	370 lm / 5 h 15 min
	Main2	160 lm / 12 h 15 min
	Main1	45 lm / 43 h
	Firefly3	6 lm / 12 d
	Firefly2	1.5 lm / 40 d
	Firefly1	0.15 lm / 200 d
	Strobe3	2500 lm / 10 Hz / 5 h 45 min (650 lm after 100 sec)
	Strobe2	2500 lm / 1 Hz / 12 h (650 lm after 9 min)
	Strobe1	160 lm / 1 Hz / 55 h
Power source		1x18650 Li-Ion
Length / head diameter / body diameter		112 mm / 33 mm / 20.4 mm
Weight without / with battery		65 g / 115 g
Ingress protection, Submersion and Impact resistance		IP68. Depth up to 10 m for 5 h. Height up to 10 m

► The model is available with White and Warm light. Light output for flashlights with Warm light is about 7% less, beam distance is about 3% less.
All the above specifications are test results based on ANSI/PLATO FL 1-2019 Standard. The data may vary due to environment, heat dissipation and other factors.