

Customer : Bürklin


Drawing No. : 1013226-50212

Seite 1 / 1

created: hs 27/05/2015 11:17:00

**Typ : GMB33310075100**

**RoHS Compliant**



$\varnothing$  D : 75 mm  
 L : 100 mm  
 a : 31,7 mm  
 h : 5 mm  
 B : M12  
 Terminals : M5

Max. torque:  
 Terminals: M5: 2,0 Nm, M6: 2,5 Nm  
 Stud: M8: 4,0 Nm, M12: 10,0 Nm

**Electrical Parameters**

Rated Capacitance ( $C_R$ ) @ 100 Hz / 20 °C	<b>33000</b> $\mu$ F	
Tolerance	<b>-10 +30</b> %	
Rated Voltage ( $U_R$ )	<b>100</b> V	
Surge Voltage ( $U_S$ ) max. 5 x 1 min / h	<b>115</b> V	
Reverse Voltage ( $U_U$ ) max. 1 s	<b>2</b> V	
Leakage Current ( $I_L$ ) @ $U_R$ / 5 min / 20 °C	<b>19800</b> $\mu$ A	
ESR typ. @ 100 Hz / 20°C	<b>9</b> m $\Omega$	
Tan $\delta$ typ. @ 100 Hz / 20°C	<b>19</b> %	
Z max. @ 10 kHz / 20°C	<b>7</b> m $\Omega$	
ESL typ.	<b>20</b> nH	
Rated Ripple Current ( $I_R$ ) @ 100 Hz / 85 °C	<b>15</b> A	
Useful life @ $I_R$ , $U_R$ , 85 °C	<b>8000</b> h	
IEC Climatic category / Standards	<b>40/085/56</b>	<b>IEC 60384-4</b>
Applications		
Your article No. / Project		