




3/2 way solenoid valve for pneumatic applications

- Compact design
- Fast switching times
- Low power consumption



Product variants described in the data sheet may differ from the product presentation and description.

Can be combined with



Type 2031 ▶
2/2 way diaphragm valve with pneumatic plastic actuator (Type CLASSIC)



Type 8640 ▶
Modular valve island for pneumatics

Type description

Type 6510 consists of a pilot flipper solenoid valve Type 6144 and a pneumatic seat valve. The flipper action system allows the switching of high pressures combined with low power consumption and short switching times. All the valves are equipped with manual override as standard. Type 6510 is extendable and, with plug connection to the rear, can be preferably used on valve island Type 8640 or, with plug connection to the front, on valve blocks for activating pneumatic actuators.

Table of contents

1. General technical data	3
2. Circuit functions	3
3. Materials	3
3.1. Chemical Resistance Chart – Bürkert resistApp.....	3
4. Dimensions	4
4.1. 3/2 way solenoid valve	4
4.2. Manifold mounting on wall or with DIN EN 50045 rail	4
5. Ordering information	5
5.1. Bürkert eShop – Easy ordering and quick delivery.....	5
5.2. Bürkert product filter	5
5.3. Ordering chart valves (3/2 way valve).....	5
5.4. Ordering chart pneumatic module Type MP01 (for 3/2 way valve).....	6
5.5. Ordering example complete valve blocks (Type 6510 with Type MP01)	6
5.6. Ordering chart accessories.....	6

1. General technical data

Product properties	
Dimensions	Detailed information can be found in chapter "4. Dimensions" on page 4.
Material	
Body	PPS, PA
Seal	FKM, NBR
Nominal diameter	DN 2.5 mm
Manual override	Standard
Performance data	
Duty cycle	Continuous operation (100 % ED)
Response times (Measurement acc. to ISO 12238)	Opening: < 15 ms Closing: < 10 ms
Electrical data	
Operating voltages	24 V DC
Voltage tolerance	± 10 %
Protection class	3 acc. to VDE 0580
Nominal power	0.8 W
Medium data	
Medium	Lubricated, oilfree, dry compressed air; neutral gases (5µm filter recommended)
Medium temperature	0 °C...50 °C
Process/Port connection & communication	
Port connection	Flange for MP01
Electric connection on valve	Rectangular plug, 2 pin, with raster 5.08 mm
Environment and installation	
Installation position	As required, preferably with actuator upright
Ambient temperature	0 °C...55 °C
Degree of protection	IP40

2. Circuit functions

Circuit functions	Description
	Type: C, solenoid valve 3/2 way Servo-controlled, with manual mode Normally closed
	Type: D, solenoid valve 3/2 way Servo-controlled, with manual mode Normally open

3. Materials

3.1. Chemical Resistance Chart – Bürkert resistApp

Bürkert resistApp – Chemical Resistance Chart

You want to ensure the reliability and durability of the materials in your individual application case? Verify your combination of media and materials on our website or in our resistApp.

Start Chemical Resistance Check


DTS 1000011060 EN Version: F Status: RL (released | freigegeben | valide) printed: 06.08.2021

4. Dimensions

4.1. 3/2 way solenoid valve

Note:


Dimensions in mm



4.2. Manifold mounting on wall or with DIN EN 50045 rail

Note:

Dimensions in mm



5. Ordering information

5.1. Bürkert eShop – Easy ordering and quick delivery



Bürkert eShop – Easy ordering and fast delivery

You want to find your desired Bürkert product or spare part quickly and order directly? Our online shop is available for you 24/7. Sign up and enjoy all the benefits.

[Order online now](#)

5.2. Bürkert product filter





Bürkert product filter – Get quickly to the right product

You want to select products comfortably based on your technical requirements? Use the Bürkert product filter and find suitable articles for your application quickly and easily.

[Try out our product filter](#)

5.3. Ordering chart valves (3/2 way valve)

Circuit function	Orifice	Q_{Nn} value air ^{1.)}	Pressure range ^{2.)}	Voltage/ Frequency	Manual over- ride	Article no. plug contact at rear ^{3.)} for Valve island Type 8640	Article no. plug contact in front ^{4.)} for valve block
	[mm]	[l/min]	[bar]	[V/Hz]			
Type: C, solenoid valve 3/2 way Servo-controlled, with manual mode Normally closed 	2.5	130	2.5...10	24 V DC	with	184041	184313
					none	184307	187605
Type: D, solenoid valve 3/2 way Servo-controlled, with manual mode Normally open 	2.5	130	2.5...10	24 V DC	with	—	184314
					none	184309	—






1.) Measured at +20 °C, 6 bar pressure at valve inlet and 1 bar pressure difference

2.) Overpressure to the atmospheric pressure

3.) At rear: Plug connection on flange side

4.) In front: Plug connection offset at 180° to flange






5.4. Ordering chart pneumatic module Type MP01 (for 3/2 way valve)

Modules Type MP01	Article no.
Connector module right, G 1/8	132409 
Connector module, without supply, left	132405 
Basic model 2 valves, push-in connection Ø 4 mm	132414 
Basic model 3 valves, push-in connection Ø 4 mm	132416 
Basic model 12 valves, push-in connection Ø 4 mm	132418 






5.5. Ordering example complete valve blocks (Type 6510 with Type MP01)

Note:

Please order the modules for block assembly from right to left (according to the example).

No.	Unit	Article no.
1	Connector module, right, G 1/8	132409 
1	Basic module, 2 valves, push-in connection Ø 4 mm	132414 
1	Basic module, 3 valves, push-in connection Ø 4 mm	132416 
1	Connector module, without supply, left	132405 
5	Valves	134281 

5.6. Ordering chart accessories

Version	Feature	Article no.
Closing plug	for plug-in coupling Ø 4 mm	781664 
Blanking plug	G 1/8	631019 
Rectangular cable plug	with 3 m cable	133486 
Rectangular cable plug	with 300 mm flying leads	644068 
Rectangular cable plug	with 2 single contacts	644067 

Bürkert – Close to You

For up-to-date addresses
please visit us at
www.burkert.com

DTS 1000011060 EN Version: F Status: RL (released | freigegeben | validé) printed: 06.08.2021

