

Signal lamp with lamp socket, BA 9s, 18.2 mm, round bezel, 250 Volt, bezel transparent, Flat quick-connect terminal 6.3 x 0.8 / 2 x 2.8 x 0.8 tin-plated



fields of application

- > Measurement-control-regulation
- > Electrical engineering
- > Mechanical and system engineering
- > Signalling systems
- > Model construction



description

Signal lamps for LEDs or filament/neon lamps with BA 9 s socket, mounting hole diameter 18.2 mm

technical data

> general

| | |
|---|-------------|
| Bezel color | transparent |
| Property of bezel / mushroom | transparent |
| Bezel shape | round |
| illuminated | Yes |
| Lamp socket | BA9s |
| Packaging unit | 10 pcs. |
| net weight | 13.2 g |
| Degree of protection, front side, according to DIN EN 60529 | IP65 |
| MOQ order | 250 pcs. |
| RoHS compliant | Yes |
| REACH compliant | Yes |

direct links

- > [RAFI eCatalog](#)

> mounting diameters

| | |
|---------------------------|---------|
| Outside dimension, length | 22 mm |
| Outside dimension, width | 22 mm |
| Outside dimension, height | 61 mm |
| Mounting hole | 18.2 mm |
| Mounting depth | 47 mm |
| Installation height | 14 mm |
| Collar dimension | 22 mm |

> mechanical data

| | |
|----------------------|--|
| Fixing | Threaded ring |
| Solderability | Yes |
| Terminal on the rear | Flat quick-connect terminal 6.3 x 0.8 / 2 x 2.8 x 0.8 tin-plated |

> **electrical data**

Operating voltage of the luminous element, max. 250 V

drawings

Mounting hole drawing