### KERN FS 2-5000Y1



# Pre-configured set consisting of the premium force gauge FS 2 and the measuring cell CO 50-Y1 $\,$



Category	
Brand	Sauter
Product categoriy	Force measurement
Product group	Force measuring device set
Product family	FS OY1

### Measuring System

Default unit	Ν
Measuring range force [Max] (N)	500 N
Readability force [d] (N)	0,1 N
Directions of force	compression
Measuring head measuring frequency	1000 Hz
Number of platforms / channels	2

#### Approval

CE mark

Display	
Display type	TFT, color
Display resolution	320×480
Languages of the user interface	German English French Spanish Italian

#### Construction

Material display housing Material housing Plastics plastic

1

Mounting - force application	Thrust piece (from
Mounting - force dissipation	customer side) 3 × threaded hole M3
Dimensions load cell (cylindrical)	20×12 mm
	20^12 11111
Functions	
Auto-off interval(s) in battery	selectable
mode/rechargeable battery mode	
Peak function	
Statistic function	1
Memory function	
Interfaces	USB-Device
Power Supply	
Input voltage power supply /	100 V - 240 V, 50 / 60
power [Max]	Hz
Input voltage device / power [Max]	5 V, 1 A
Plug-in power supply type	USB including power supply
Supplied power supply	Battery & Power supply
Plug-in power supply / adapter for	
countries - included with the	EURO
delivery	
Rechargeable battery charging time	8 h
Rechargeable battery operating	
time - backlight on	5 h
Rechargeable battery operating	8 h
time - backlight off	
Battery / accumulator type	Li-Ion
Battery connection	2-pole tub connector
Battery capacity	2.400 mAh
Battery voltage	3,7 V
Packing & Shipping	
Readability force [d] (N)	3 d
Net weight	0,349 kg
Shipping method	Parcel service
Net weight approx.	0,35 kg
Gross weight approx.	1,4 kg
Shipping weight	1,245 kg
Services (optional)	
Article number for DAkkS	963-261
calibration (compressive force)	


## KERN FS 2-5000Y1



Pre-configured set consisting of the premium force gauge FS 2 and the measuring cell CO 50-Y1  $\,$ 

Pictograms

STANDARD



**OPTION** 

