

KERN 347-075-100

KERN

Supporting bar, OIML Class M1, 100 g, stainless steel fine turned



Category

Brand	KERN
Product category	Individual weight
Product group	Supporting Bar
Product family	347

Measuring System

Test weight - volume (cm ³)	11,9048
Test weight - Density uncertainty (kg/m ³)	100
Test weight - volume uncertainty (cm ³)	0,2409
Weight OIML class	M1
Test weight - nominal value	100 g
Permissible tolerance according to OIML (+/-)	5 mg
Test weight - Density (kg/m ³)	8000
OIML-compliant	✓
Test weight - Density [Min] (OIML)	2600

Construction

Shape weight	Supporting bar (Type A)
Dimensions (Ø×H)	26×240 mm
Material	stainless steel fine turned
Max. total weight	2 kg
Max. single weight	1 kg
Adjustment method	Adjusting cavity - screwed

Services (optional)

Article number for DAkkS calibration	962-637
--------------------------------------	---------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	26×26×240 mm
Shipping method	Parcel service
Net weight approx.	0,10 kg
Gross weight approx.	0,10 kg
Shipping weight	0,1 kg

Product information

GTIN/EAN number	4045761256323
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

