
KERN **KBP 60V20M**

Platform: weighing plate of stainless steel, painted steel base, silicone-coated aluminium load cell with protection against dust and water splashes IP65



Category	
Brand	KERN
Product categoriy	Component
Product group	Platform
Product family	KBP-V20-IP65

Measuring System	
Weighing capacity [Max]	30 kg; 60 kg
Readability [d]	2 g
Minimum weight [Min]	200 g; 400 g
Load cell connection	4-wire
Load cell - Resolution (verifiable)	2 × 3000 e
Loadcell type	aluminium IP65 silicone-coated

Construction	
Dimensions weighing surface (W×D)	400×300 mm
Dimensions weighing surface	400×300 mm
Dimensions weighing platform (W×D×H)	400×300×110 mm
Material weighing plate	stainless steel
Material platform	steel, lacquered
Material load cell(s)	aluminium
Levelling feet adjustable	✓
Cable length	2,5 m
Allowed cable length display device [Max]	3 m
Platform Construction	Single-Cell
Load cells - number	1

Functions	
IP protection - load cell	IP65

Environmental conditions	
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

Approval	
Conformity assessment possible ex works	✓
Verification scale interval [e]	10 g; 20 g

Services (optional)	
Article number for conformity assessment	965-229
Article number for DAkkS calibration	963-129

Packing & Shipping	
Delivery time	1 d
Dimensions packaging (W×D×H)	870×460×190 mm
Shipping method	Parcel service
Net weight approx.	8 kg
Gross weight approx.	9 kg
Shipping weight	15,2 kg

Product information	
GTIN/EAN number	4045761475854
REACH classification	no prohibited substances

Pictograms

STANDARD



FACTORY

