
KERN KFP 3000V20LNM



Weighing bridge made from steel, also with weighing plate screwed on from the top



Category	
Brand	KERN
Product categoriy	Component
Product group	Weighing bridge
Product family	KFP-V20-IP67

Measuring System	
Weighing capacity [Max]	3000 kg
Readability [d]	1 kg
Minimum weight [Min]	20 kg
Load cell connection	6-wire

Approval	
Accuracy classe	III
Verification scale interval [e]	1 kg
Conformity assessment possible ex works	✓

Construction	
Dimensions weighing platform (W×D×H)	1500×1500×80 mm
Material weighing plate	steel, lacquered
Material platform	steel, varnished
Dimensions weighing surface (W×D)	1500×1500 mm
Cable length	5 m
Allowed cable length display device [Max]	20 m
Material load cell(s)	aluminium
Load cells - number	4
Levelling feet adjustable	✓

Functions	
IP protection - load cell	IP67

IP protection - platform IP6

Environmental conditions		
Ambient temperature [Max]	40 °C	

Packing & Shipping	
Readability force [d] (N)	2 d
Dimensions packaging (W×D×H)	1610×1570×360 mm
Net weight	171 kg
Shipping method	Freight
Net weight approx.	175 kg
Gross weight approx.	235 kg
Shipping weight	234 kg

Services (optional)		
Article number for conformity assessment	965-232	
Article number for DAkkS calibration	963-132	

Pictograms

STANDARD



FACTORY

