


KERN KFP 600V20AM



Platform: weighing plate of stainless steel, painted steel base, silicone-coated aluminium load cell with protection against dust and water splashes IP65



Category

Brand	KERN
Product category	Component
Product group	Platform

Measuring System

Weighing capacity [Max]	600 kg
Readability [d]	20 g
Minimum weight [Min]	4 kg
Loadcell type	aluminium silicone-coated
Load cell connection	6-wire

Approval

Verification scale interval [e]	200 g
Conformity assessment possible ex works	✓

Construction

Dimensions weighing platform (W×D×H)	800×600×189 mm
Material weighing plate	stainless steel
Material platform	steel, varnished
Dimensions weighing surface (W×D)	800×600 mm
Cable length	2,5 m
Allowed cable length display device [Max]	20 m
Material load cell(s)	aluminium
Load cells - number	1
Levelling feet adjustable	✓

Functions

IP protection - load cell	IP65
---------------------------	------

Packing & Shipping


Readability force [d] (N)	2 d
Dimensions packaging (W×D×H)	850×1250×240 mm
Net weight	41,8 kg
Shipping method	Freight
Net weight approx.	42 kg
Gross weight approx.	55 kg
Shipping weight	55 kg

Services (optional)

Article number for conformity assessment	965-230
Article number for DAkkS calibration	963-130

Pictograms

STANDARD



FACTORY

