

# KERN FS 2-2KOY1



Pre-configured set consisting of the premium force gauge FS 2 and the measuring cell CO 200-Y1



Mounting - force application	Thrust piece (from customer side)
Mounting - force dissipation	3 × threaded hole M3
Dimensions load cell (cylindrical)	20×12 mm

## Functions

Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
Peak function	✓
Statistic function	✓
Memory function	✓
Interfaces	USB-Device

## Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	5 V, 1 A
Plug-in power supply type	USB including power supply
Supplied power supply	Battery & Power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
Rechargeable battery charging time	8 h
Rechargeable battery operating time - backlight on	5 h
Rechargeable battery operating time - backlight off	8 h
Battery / accumulator type	Li-Ion
Battery connection	2-pole tub connector
Battery capacity	2.400 mAh
Battery voltage	3,7 V

## Packing & Shipping

Readability force [d] (N)	3 d
Net weight	0,349 kg
Shipping method	Parcel service
Net weight approx.	0,35 kg
Gross weight approx.	1,4 kg
Shipping weight	1,242 kg

## Services (optional)

Article number for DAkkS calibration (compressive force)	963-262
--	---------

## Category

Brand	Sauter
Product category	Force measurement
Product group	Force measuring device set
Product family	FS OY1

## Measuring System

Default unit	N
Measuring range force [Max] (N)	2 kN
Readability force [d] (N)	0,4 N
Directions of force	compression
Measuring head measuring frequency	1000 Hz
Number of platforms / channels	2

## Approval

CE mark	✓
---------	---

## Display

Display type	TFT, color
Display resolution	320×480
Languages of the user interface	German English French Spanish Italian

## Construction

Material display housing	Plastics
Material housing	plastic


# KERN FS 2-2KOY1



Pre-configured set consisting of the premium force gauge FS 2 and the measuring cell CO 200-Y1

## Pictograms

### STANDARD



### OPTION

