

# KERN ORM 1NA

# KERN

Digital measurement of refraction index for universal application



## Category

Brand	Optics
Product category	Refractometer
Product group	Digital refractometer
Product family	ORM-NA

## Measuring System

Automatic temperature compensation (ATC)	✓
Measuring method	Total reflection
Area of application	Salt
Appropriate calibration liquid	0 % (distilled water)
Measurement temperature [Min] (°C)	0 °C
Measurement temperature [Max] (°C)	40 °C
Brix scale	✓
Readout Brix	0,1 %
Measuring range Brix [Min]	0 %
Measuring range Brix [Max]	50 %
Accuracy Brix	±0,2 %
Scale for Refractive index	✓
Readout refractive index	0,0001 nD
Measuring range refractive index [Min]	1,3330 nD
Measuring range refractive index [Max]	1,4200 nD
Accuracy refractive index	±0,0003 nD
Scale salinity (NaCl) %	✓
Readout salinity (NaCl) %	0,1 %
Measuring range salinity (NaCl) % [Min]	0 %
Measuring range salinity (NaCl) % [Max]	28 %
Accuracy salinity (NaCl) %	±0,2 %

Scale salinity (NaCl) ‰	✓
Readout salinity (NaCl) ‰	1 ‰
Measuring range salinity (NaCl) ‰ [Min]	0 ‰
Measuring range salinity (NaCl) ‰ [Max]	280 ‰
Accuracy salinity (NaCl) ‰	±2 ‰
Scale salinity (spec. weight)	✓
Readout salinity (spec. weight)	0,001
Measuring range salinity (spec. weight) [Min]	1,000
Measuring range salinity (spec. weight) [Max]	1,220
Accuracy salinity (spec. weight)	±0,002

## Approval

CE mark	✓
---------	---

## Construction

Dimension (W×D×H)	121×58×25 mm
Refractometer type	Handheld refractometer
Scale - Display type	Digital

## Functions

Auto-off interval(s) in battery mode/rechargeable battery mode	60 sec
IP protection - complete device	IP65
Automatic temperature compensation	✓

## Power Supply

Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery connection	Pad + Spring
Battery capacity	1.300 mAh
Battery voltage	1,5 V

## Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

## Packing & Shipping

Dimensions transport container (W×D×H)	170×110×50 mm
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	170×110×50 mm
Net weight	0,14 kg
Shipping method	Parcel service

# KERN ORM 1NA



Digital measurement of refraction index for universal application

Net weight approx.	0,15 kg
Gross weight approx.	0,35 kg
Shipping weight	0,31 kg

## Services (optional)

Article number for factory calibration	961-290
--	---------

## Pictograms

### STANDARD

