

KERN ORM 2SU

Digital measurement of refraction index for universal application

KERN



Category

Brand	Optics
Product category	Refractometer
Product group	Digital refractometer
Product family	ORM-SU

Measuring System

Measurement temperature [Min] (°C)	0 °C
Measurement temperature [Max] (°C)	40 °C
Precision	0,2 %
	0,2 %
	0,2 %
	0,2 %
Measuring method	Total reflection
Measuring range Brix [Min]	0 %

Scales	Brix
	Laktose (Milchzucker)
	Maltose (Malzzucker)
	Dextran

Measuring ranges	0,0 % - 50,0 %
	0,0 % - 16,5 %
	0,0 % - 15,6 %
	0,0 % - 10,6 %

Readabilities [d]	0,1 %
	0,1 %
	0,1 %
	0,1 %
Readout Brix	0,1 %

Automatic temperature compensation (ATC)	✓
--	---

Accuracy Brix	±0,2 %
Measuring range dextran [Min]	0 %
Measuring range dextran [Max]	11 %
Readout dextran	0,1 %

Accuracy dextran	±0,2 %
Scale for dextran	✓
Measuring range lactose (milk sugar) [Min]	0 %
Measuring range lactose (milk sugar) [Max]	17 %
Readout lactose (milk sugar)	0,1 %
Accuracy lactose (milk sugar)	±0,2 %
Measuring range maltose (malt sugar) [Min]	0 %
Measuring range maltose (malt sugar) [Max]	16 %
Readout maltose (malt sugar)	0,1 %
Accuracy maltose (malt sugar)	±0,2 %
Scale lactose (milk sugar)	✓
Scale maltose (malt sugar)	✓
Appropriate calibration liquid	0 % (distilled water)
Measuring range Brix [Max]	50 %
Brix scale	✓
Area of application	Sugar

Construction

Dimension (W×D×H)	121×58×25 mm
Refractometer type	Handheld refractometer
Scale - Display type	Digital
Prism lid	✓
Material prism	ZLaF3 lanthanum flint glass nd=1.85544

Functions

Averaging measurement	✓
Averaging measurement amount	15
IP protection - complete device	IP65
Auto-off interval(s) in battery mode/rechargeable battery mode	60 sec

Power Supply

Supplied power supply	Battery
Power supply cable removable	removable
Battery / accumulator type	Alkali(-Manganese)
Battery connection	Pad + Spring
Battery capacity	1.300 mAh
Battery voltage	1,5 V
Battery - Number of cells	1
Battery - Individual weight	11,5 g
Battery - Total weight	11,5 g
Battery - Construction	Individual cells
Battery capacity (Wh)	1,95 Wh

KERN ORM 2SU



Digital measurement of refraction index for universal application

Battery – Lithium content	0 g
Battery/Accu connected	not connected, enclosed

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for factory calibration	961-290
--	---------

Packing & Shipping

Dimensions transport container (W×D×H)	170×110×50 mm
Delivery time	1 d
Dimensions packaging (W×D×H)	170×110×50 mm
Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,35 kg
Shipping weight	0,31 kg

Product information

GTIN/EAN number	4045761335608
REACH classification	no prohibited substances

Pictograms

STANDARD

