

NAC3FX-W-TOP-L

Locking female cable connector for big power cord with outer diameters from 10–16 mm (0.39 – 0.63 inches) such as H07RN-F3G2.5 or SOOW 12/3, SOOW 14/3 and SJ00W 12/3. Certified according to EN/UL & CSA 60320-1.

Keyed for Power IN, screw terminals, IP65, up to 16 A (USA: 20A)

The powerCON TRUE1 TOP is a single-phase connector for outdoor applications with breaking capacity (CBC) for outdoor applications.





Features & Benefits

- | | |
|---|--|
| <ul style="list-style-type: none">• IEC EN 60320-1, UL 60320-1 and C22.2 No. 60320-1:19 certified, thus accepted as a component for cord sets acc. to IEC 60799 / UL817 and equipment acc. to IEC 62368-1 | <ul style="list-style-type: none">• Unique NEUTRIK locking bushing and strain relief for cable diameters 10 mm to 16 mm (0.39 – 0.63 inches) |
| <ul style="list-style-type: none">• Heavy duty sealed power connector for harsh and demanding environment | <ul style="list-style-type: none">• IP65 rating and approved for outdoor protection |
| <ul style="list-style-type: none">• Uses high impact UV-resistant materials | <ul style="list-style-type: none">• Extremely robust and reliable cable retention |
| <ul style="list-style-type: none">• TOP True Outdoor Protection | <ul style="list-style-type: none">• Lockable, single phase connector with Circuit Breaking Capability (16A resp. 20 A 250 VAC) |
| <ul style="list-style-type: none">• Superior NEUTRIK quality standard | |

Assembly

Features powerCON® TRUE1® L

Product related questions and answers

Question	Answer
How are the certifications different to the current version NAC3*X-W-TOP?	EN certification: Both versions are certified according to EN 60320-1. The new L-version however is certified for large cables as follows: H07RN-F 3G 2,5 mm² The old version is certified for cable types: H07RN-F 3G 1,5 mm² and H05VV-F 3G 1,0 - 2,5 mm² UL certification: The new L-version is certified according to UL 60320-1 for cables SOOW 12/3 and SOOW 14/3. The old version is certified according to UL 498. JET certification: Both versions are JET certified.
When is the IEC 60799 relevant?	This standard applies for "Cord Sets And Interconnection Cord Sets" and therefore covers cables to the mains and cables acting as power interconnections.
Why is the bushing loose in one direction?	This is to meet the standards requirement to prevent disassembling by hand. In order to open the cable entry a special tool will be required.

Technical Information

Product	
Title	NAC3FX-W-TOP-L
Connector series	powerCON TRUE1 TOP

Electrical	
Dielectric strength	2.8 kVac
Insulation resistance	> 0.1 GΩ
Number of electronical contacts	2 + PE
Rating Europe	IEC EN 60320-1: 16 A 250 V AC
	Certified with cable types: H07RN-F3G2.5
Rating USA	UL 60320-1 & C22.2 No. 60320-1:19: 20 A 250 V AC
	Certified with cable types:
	- SOOW 12/3, SOOW 14/3
	- SJOOW 12/3

Mechanical	
Cable O.D.	10 – 16 mm (0.39 – 0.63 inches)
Lifetime	Typically 5'000 mating cycles
Wire size (mm²)	2.5 mm²
Wire size (AWG)	14 – 12 AWG

Material	
Contact plating	2 µm Ag
Contacts	Bronze (CuSn0.2)
Insert	Polyamide (PA 6.6 30 % GR)
Locking element	ZuAl4Cu1
Shell	Polyamide (PA 6.6 30 % GR)
Strain relief	Polyacetal (POM)

Environmental	
Flammability	UL 94 V-0
Protection class	IP65, UL50E enclosure type 4 (mated)
Temperature range	-30 °C to +80 °C