

IoT ready

NEXT LEVEL Easy Touch FUNCTIONS



1

Discover more details and matching accessories online!

Stainless steel display device with IP68 dust and spray protection and up to four interfaces, with optional verification

Features

- With dust and spray protection (IP68), which makes it ideal for use in industry and outdoors
- Standardised, convenient KERN concept of operation, consistency across products in terms of design, menu structure, button functions, interface connection and interface protocol
- Industry 4.0: The exchange of data and control commands is optional using up to four interfaces to suit individual requirements: two wired connections (RS-232, Ethernet, USB or analogue module) and two wireless connections (WiFi, Bluetooth)
- Each interface can be set up separately, e.g.:
  - Interface 1 (WiFi): Continuous sending to a PC for documentation of a process
  - Interface 2 (RS-232): Print stable weight
  - Interface 3 (analogue module): Controlling a device when the target weight is reached
  - Interface 4 (Bluetooth): Continuous sending to a tablet to monitor a process
- Data query and remote control of the balance using a computer or CRM/ERP systems using the KERN Communication Protocol
- Available as an option with alibi memory for paperless archiving of weighing results. This also means the results of weighings with mandatory verification can be electronically evaluated and processed further, see *internet*

*Note: Only two wired connections (RS-232, Ethernet, USB or analogue module) and two wireless connections (WiFi, Bluetooth) can be used at the same time

STANDARD



OPTION



FACTORY



KERN	KXC-TM
Display (segments)	6 digits
EU type approval	Yes
Resolution verifiable (e)	3.000
Terminal resolution (not verifiable)	999.999
Weighing capacities	2
Weighing units	kg, g, lb, ffa, PCS, % | Verifiable: kg, g
Digit increments	5, 10, 20, 50, n
Piece counting with reference	n
Display, digit height	LCD, 48 mm
Display backlight	yes
Strain gauge load cells	87 – 1227 Ω
Linearisation (points)	3
Input voltage	110 V - 240 V AC
Permissible ambient temperature	-10 °C – 40 °C
Dimensions housing W×D×H	232×150×77,3 mm
Net weight	1,6 kg