

KERN ORM 2WN

KERN

Digital measurement of refraction index for universal application



Category

Brand	Optics
Product category	Refractometer
Product group	Digital refractometer
Product family	ORM-WN

Measuring System

Automatic temperature compensation (ATC)	✓
Measuring method	Total reflection
Area of application	Wine
Percentage by volume	0,0-22,0%(v/v) @ 0,1% (v/v) ± 0,2%(v/v)
Appropriate calibration liquid	0 % (distilled water)
Measurement temperature [Min] (°C)	0 °C
Measurement temperature [Max] (°C)	40 °C
Brix scale	✓
Readout Brix	0,1 %
Measuring range Brix [Min]	0 %
Measuring range Brix [Max]	50 %
Accuracy Brix	±0,2 %
Scale KMW (Babo)	✓
Readout KMW (Babo)	0,1 °KMW
Measuring range KMW (Babo) [Min]	0 °KMW
Measuring range KMW (Babo) [Max]	25 °KMW
Accuracy KMW (Babo)	±0,2 °KMW
Scale Oechsle	✓
Readout Oechsle	1 °Oe
Measuring range Oechsle [Min]	0 °Oe
Measuring range Oechsle [Max]	230 °Oe
Accuracy Oechsle	±2 °Oe

Scale volume percentage	✓
Readout volume percentage	0,1 %
Measuring range volume percentage [Min]	0 %
Measuring range volume percentage [Max]	22 %
Accuracy volume percentage	±0,2 %

Approval

CE mark	✓
---------	---

Construction

Dimension (W×D×H)	121×58×25 mm
Refractometer type	Handheld refractometer
Scale - Display type	Digital

Functions

Auto-off interval(s) in battery mode/rechargeable battery mode	60 sec
IP protection - complete device	IP65
Automatic temperature compensation	✓

Power Supply

Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery connection	Pad + Spring
Battery capacity	1.300 mAh
Battery voltage	1,5 V

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Dimensions transport container (W×D×H)	170×110×50 mm
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	170×110×50 mm
Net weight	0,14 kg
Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,35 kg
Shipping weight	0,31 kg

KERN ORM 2WN



Digital measurement of refraction index for universal application

Services (optional)

Article number for factory calibration	961-290
--	---------

Pictograms

STANDARD

