KERN SXC 300K-2



Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory



Category	
Brand	KERN
Product categoriy	Industrial scale
Product group	Stainless steel platform scale
Product family	SXC

Measuring System	
Construction type of the scale	Single-range balance
Number of weighing ranges	1
Weighing system	Strain gauge
Weighing capacity [Max]	300 kg
Readability [d]	0,02 kg
Resolution	15.000
Linearity	± 0,06 kg
Reproducibility	0,02 kg
Default unit	kg
Units	kg g lb ffa PCS %
Adjustment options	Adjusting with external weight
Recommended adjusting weight	300 kg (M1)
Possible calibration points	300 kg
Stabilization time	3 s
Warm-up time	30 min
Eccentric loading at 1/3 [Max]	0,0005 kg
Maximum creep (15 minutes)	80 g
Maximum creep (30 minutes)	160 g
Loadcell type	stainless steel IP68 encapsulated
Load cell connection	6-wire

Approval	
CE mark	✓

Display	
Display type	LCD
Display type	LCD with backlight
Display screen size	160×60 mm
Display backlight	✓
Display digit height	48 mm
Languages of the user interface	English Symbol language

Construction	
Dimension display device (W×D×H)	232×150×80 mm
Dimensions weighing platform (W×D×H)	650×500×136 mm
Material display housing	stainless steel
Material weighing plate	stainless steel
Material platform	Stainless steel
Dimensions weighing surface (W×D)	650×500 mm
Cable length	3 m
Display device cable length	3 m
Allowed cable length display device [Max]	20 m
Material load cell(s)	stainless steel
Load cells - number	1
Levelling feet adjustable	✓
Wall mount	✓

Functions	
Number of keys for operation	7
Auto-off interval(s) in mains power mode	off
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min 2 min 1 min 30 min 60 min 30 sec
Capacity display	✓
PreTare function	✓
Tare function	manual (multi)
Hold function	✓
Percentage determination	✓
Counting function	✓
Tolerance weighing	✓

1

KERN SXC 300K-2



Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory

Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Sum A
Sum memory function	✓
Alibi memory	optional internal memory
Alibi memory - number of memory spaces	250.000
Interfaces	RS-232 (optional, factory) Bluetooth (optional, factory) Ethernet (optional, factory) WiFi (optional, factory) Alibi memory (optional, factory) analogue (0 - 10 V) (optional, factory) analogue (4 - 20 mA) (optional, factory) Bluetooth BLE (v4.0) (optional, factory) USB-Device (optional, factory)
IP protection - complete device	-
IP protection - display	IP68
IP protection - load cell	IP68
IP protection - platform	no IP protection
Counting	
Smallest piece weight when piece counting - laboratory conditions	10 g
Smallest piece weight when piece counting - normal conditions	100 g
Counting reference weight can be entered	✓
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Counting resolution (laboratory conditions)	30.000
Power Supply	
Input voltage power supply / power [Max]	110 V - 240 V AC
Plug-in power supply type	Built-in power supply
Supplied power supply	Power supply unit
Plug-in power supply / adapter for	ELIDO

EURO

countries - included with the

delivery

Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	8 h
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	48 h
Battery	no battery
Battery / accumulator type	Li-lon
Environmental conditions	
Humity of environment [Min]	0 %
Humity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Packing & Shipping	
Packing & Shipping Readability force [d] (N)	1 d
	1 d 1050×675×250 mm
Readability force [d] (N)	
Readability force [d] (N) Dimensions packaging (W×D×H)	1050×675×250 mm
Readability force [d] (N) Dimensions packaging (W×D×H) Net weight	1050×675×250 mm 36 kg
Readability force [d] (N) Dimensions packaging (W×D×H) Net weight Shipping method	1050×675×250 mm 36 kg Parcel service
Readability force [d] (N) Dimensions packaging (W×D×H) Net weight Shipping method Net weight approx.	1050×675×250 mm 36 kg Parcel service 36 kg
Readability force [d] (N) Dimensions packaging (W×D×H) Net weight Shipping method Net weight approx. Gross weight approx.	1050×675×250 mm 36 kg Parcel service 36 kg 38 kg
Readability force [d] (N) Dimensions packaging (W×D×H) Net weight Shipping method Net weight approx. Gross weight approx. Shipping weight	1050×675×250 mm 36 kg Parcel service 36 kg 38 kg
Readability force [d] (N) Dimensions packaging (W×D×H) Net weight Shipping method Net weight approx. Gross weight approx. Shipping weight Services (optional) Article number for adjustment at	1050×675×250 mm 36 kg Parcel service 36 kg 38 kg 38 kg
Readability force [d] (N) Dimensions packaging (W×D×H) Net weight Shipping method Net weight approx. Gross weight approx. Shipping weight Services (optional) Article number for adjustment at the location of installation Article number for DAkkS	1050×675×250 mm 36 kg Parcel service 36 kg 38 kg 38 kg

KERN SXC 300K-2



Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory

Pictograms

STANDARD







DMS 1 DAY

FACTORY

