

KERN TN GOLD 80

Ultrasonic measuring instrument for checking the authenticity of gold bars and coins



Display type	LCD
Display digit height	14 mm

Construction	
Dimension (W×D×H)	150×74×32 mm
Dimension display device (W×D×H)	150×74×32 mm
Dimension housing (W×D×H)	150×74×32 mm
Dimensions completely mounted (W×D×H)	150×74×32 mm
Material display housing	Plastics
Material housing	plastic
Cable length	0,9 m

Functions	
Auto-off interval(s) in battery mode/rechargeable battery mode	1 - 60 min
Interfaces	USB-Device

Power Supply	
Supplied power supply	Battery
Battery	2×1.5 V AA
Battery / accumulator type	Alkali(-Manganese)
Battery connection	Pad + Spring
Battery capacity	3.000 mAh
Battery voltage	1,5 V
Battery operating time	100 h

Environmental conditions	
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	375×220×95 mm
Net weight	0,245 kg
Shipping method	Parcel service
Net weight approx.	0,25 kg
Gross weight approx.	1,4 kg
Shipping weight	1,6 kg

Services (optional)	
Article number for factory calibration	961-113

Category	
Brand	Sauter
Product category	Material thickness measuring device
Product group	Ultrasonic Material thickness gauge pulse-echo method
Product family	TN-GOLD

Measuring System	
Units	mm inch
Tolerance (% of [Max])	0,5%
Readability material thickness [d] (mm)	0,01 mm
Speed of sound [Min] (m/s)	1000 m/s
Speed of sound [Max] (m/s)	9999 m/s
Material thickness pulse-echo [Min] (mm)	0,75 mm
Material thickness pulse-echo [Max] (mm)	80 mm
Measuring head diameter	6 mm
Measuring head measuring frequency	7 MHz
Internal data memory: Number of value groups	20
Internal data memory: Number of individual values	100

Approval	
CE mark	✓

Display	
Display type	LCD


KERN TN GOLD 80



Ultrasonic measuring instrument for checking the authenticity of gold bars and coins

Pictograms

STANDARD



OPTION

