




Data Sheet

CAM switch

Version 10/24



	LW26-20 6C04/2C55I	
	0	1
	0°	60°
1 — 2		×
3 — 4		×
5 — 6		×
7 — 8		×

Data Sheet

Specification

Switch rating

Ui	Ith	Ue	AC-21A	AC-23A	AC-23A	AC-2	AC-3	AC-4	AC-15	AC-23A
			Ie	Ie	Ie	Ie	Ie	Ie	Ie	Ie
690V	20A	AC 440V	20A	20A	7.5KW	7.5KW	5.5KW	1.5KW	4A	
		DC 240V							5A	1A

Mechanical life

Without load: 8500 times; with load: 1500 times; the total number of operating cycles is 10,000 times

Working conditions

1.-5 °C~ 40 °C, and the average temperature within 24 hours does not exceed 35 °C.

2.Should not be installed above 2000m above sea level.1-3.The humidity should not exceed 50% when the ambient temperature is 40 °C and higher humidity is allowed for lower temperature, for example, it can reach 90% at 20 °C.