

MKAS 355

Metal chop saw

Saw safely with speed and precision with the chop saw for metal.

Part number: 7 236 54 60 00 0



FEIN benefits

- > Up to 100% non-sparking: cold cuts for safe working without dust.
- > Fast and precise dividing: maximum work progress with minimal rework.
- > A versatile all-rounder: the right saw blade for every material.
- > Angle can be set to 0–45° for mitre cuts.
- > Quick clamping device for table clamp.
- > Depth stop
- > Swarf collecting vessel.
- > Dead man's switch.

Supplied

- ✓ 1 saw blade for construction steel
- ✓ 1 combination wrench: 6 mm hexagon socket and PH2 cross recess
- ✓ 1 socket head wrench 8 mm
- ✓ 1 pair of extra carbon brushes

Application

Installation work



Workshop jobs



★ suitability

★★ optimal suitability

Technical data

GENERAL TECHNICAL DATA

Current/Voltages	230 V
Input	1,800 W
Output	1,050 W
Speed, no load	1,300 rpm
Holder mandrel	25.4 mm
Saw blade Ø	355 mm
Max. cutting depth, square	120 mm
Max. cutting depth, square at 45°	90 mm
Max. cutting depth, round	100 mm
Max. cutting depth, round at 45°	90 mm
Cable with plug	4 m
Weight	24.4 kg

VIBRATION AND NOISE EMISSION VALUES

Sound pressure level LpA	95,3 dB
Uncertainty of measured value KpA	3 dB
Sound power level LWA	106,3 dB
Uncertainty of measured value KWA	3 dB
Sound peak value LpCpeak	110,9 dB
Uncertainty of measured value KpCpeak	3 dB
Vibration value 1 dhv 3-way	ah = 2,7 m/s ²
Uncertainty of measured value Kα	1,5 m/s ²

Examples of use

