



DATASHEET

ESD PE Foam



Technical data

Item No.	Dimensions (mm)
3069296	253 x 353 x 3
3069297	253 x 153 x 3
3069298	300 x 300 x 6
3069299	253 x 353 x 10
3069300	138 x 55 x 5
3088153	253 x 153 x 10
3088154	253 x 153 x 6
3088155	253 x 353 x 6
3088156	150 x 75 x 5
3594624	465 x 345 x 10
3594625	510 x 390 x 10
3594626	365 x 265 x 10
3594627	560 x 460 x 20



Material.....Raw material: Polyethylene Resin (75 - 85%)
Filler: Conductive Carbon Black (10 - 15%)
Blowing Agent: AC foaming (5 - 15%)
Processing Agent: Others (3 - 6%)

Color.....Black

Density.....40 - 60 kg/m³

Surface Resistivity.....10(6) - 10(9) Ω/sq

Volume Resistivity.....10(6) - 10(9) Ω•cm

Abrasive Potential.....<100 V

Operating conditions.....0 to +40 °C, 0 - 85% (relative, non-condensing)

Storage conditions.....-20 to +40 °C, 0 - 85% (relative, non-condensing)