

Datasheet

Manufacturer Part No.: T24CA048 ... T24CA055

Soft-Grip-Texture-Shrinking-Tubes 1.5 m Item-No.: T24CA048 ... T24CA055



This shrinking tube with textured “Soft-Grip” surface is ideally suited to increase or restore the grip of handles. Furthermore, the pattern gives a great look. Perfect for tennis rackets, fishing rods, tools, bicycles, pool cues, field hockey sticks or any other application! The product is designed to last and that is why it is made of high purity polyolefin. Optimal results can be achieved by a shrinking process with a heat gun or similar - open flames are not suitable for this purpose!

Technical Specifications

Shrink ratio: 2:1 • Shrinking temp.: 90 ... 120 °C • Temperature range: -50 ... 120 °C • Material: Polyolefin • Tensile strength: > 10.4 MPa • Color: Black (textured) • Length: 1.5 m per unit.

Versions

| Part-No. | Description | Inner Ø before shrink (appx.) | Inner Ø after shrink (appx.) | Content | EAN / GTIN |
|----------|--|-------------------------------|------------------------------|---------|---------------|
| T24CA048 | Soft-Grip-Texture-Shrinking-Tube Ø 15 mm Black | 15 mm | 8 mm | 1.5 m | 4260732286134 |
| T24CA049 | Soft-Grip-Texture-Shrinking-Tube Ø 20 mm Black | 20 mm | 10 mm | 1.5 m | 4260732286141 |
| T24CA050 | Soft-Grip-Texture-Shrinking-Tube Ø 25 mm Black | 25 mm | 13 mm | 1.5 m | 4260732286158 |
| T24CA051 | Soft-Grip-Texture-Shrinking-Tube Ø 30 mm Black | 30 mm | 15 mm | 1.5 m | 4260732286165 |
| T24CA052 | Soft-Grip-Texture-Shrinking-Tube Ø 35 mm Black | 35 mm | 18 mm | 1.5 m | 4260732286172 |
| T24CA053 | Soft-Grip-Texture-Shrinking-Tube Ø 40 mm Black | 40 mm | 20 mm | 1.5 m | 4260732286189 |
| T24CA054 | Soft-Grip-Texture-Shrinking-Tube Ø 45 mm Black | 45 mm | 23 mm | 1.5 m | 4260732286196 |
| T24CA055 | Soft-Grip-Texture-Shrinking-Tube Ø 50 mm Black | 50 mm | 25 mm | 1.5 m | 4260732286202 |

Please shrink with a heat gun or similar - open flames are not suitable for this purpose! Products are not for children!

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval of the editor. Reprinting, also in part, is prohibited. The publication represents the technical status at the time of printing. All statements without guarantee.