

Flexible Solar Balcony Power Plant 600W WIFI TX-270






Plug & Play

800W Inverter

6x 105W Solar Panel

5m Connection cable

WiFi



- Mount on balcony, fence and more
- Easy installation thanks to lightweight solar modules
- Flexible solar modules (without glass - EVA material)
- Lightweight and compact microinverter
- Suitable for feeding electricity into the 230V household grid
- Maximum inverter feed-in power of 800W
- Ideal for covering the base load of your home during the day
- Power tracking possible via app and web view

Technical Specifications:

- Solarpanel: Monocrystalline half cells
- Cable connection: MC4
- Max. power: 6x 105W
- Operating voltage: 20.6V
- Operating current: 5.11A
- Module efficiency: 18.3%
- Operating temperature: -40°C ~ +85°C

Micro Inverter 800W

- Configured to 600W, automatic update after change of law
- Nominal output power: 800VA
- Nominal output current: 3.48A
- Nominal output voltage: 230V
- Operating temperature: -40°C - +65°C
- Transmission: Built-in WiFi
- Frequency range: 2.412 - 2.472GHz
- Radiated transmit power: max. 18.4dBm / 69.2mW
- Weight (total) / Dimensions (single panel): 22kg / 104 x 58 x 2cm

Compatibility:

App "S-Miles Installer": iOS 13.0 or above; Android 10.0 or above / EN, DE, FR, ES, IT, NL, CZ, PL, PO (10-2023)

Package Contents:

1x PV Micro Inverter 800W, 6x Solar panel 105W, 1x 5m connection cable, mounting material (60x plastic strap / 36x metal band), MC4 extension cable (2x 2m-set & 1x 3m-set), 2x MC4 Y-splitter, user manual

Article No. 5117

