



TOOLCRAFT

DATASHEET

110-Piece Set of Taps and Dies, Tungsten Steel, Metric Sizes

Item No. 3304388

Overview



Features

- Hardened alloy steel for maximum strength, durability and longevity
- Heavy-duty plastic blow-molded carrying case
- Tapered teeth design
- Suitable for the repair of new threads or damaged threads

Technical data

Material	Hardened steel alloy Tungsten
Product type	Tap and die set
Thread sizes	M2 to M18
Case dimensions (W x H x D)	440 x 330 x 50 mm
Weight	5.7 kg

Parts

DIN2181 Taps

2×0.4	3×0.5	4×0.7	5×0.8	6×0.75	6×1	7×0.75	7×1
8×0.75	8×1	8×1.25	9×0.75	9×1	9×1.25	10×0.75	10×1
10×1.25	10×1.5	11×0.75	11×1	11×1.25	11×1.5	12×0.75	12×1
12×1.25	12×1.56	12×1.75	14×1	14×1.25	14×1.5	14×2	16×1
16×1.5	16×2	18×1.5					

DIN223 Dies (25.4 mm DIA.)

2×0.4	3×0.5	4×0.7	5×0.8	6×1	7×1	8×1.25	9×1.25
6×0.75	7×0.75	8×0.75	8×1	9×0.75	9×1		

DIN223 Dies (25.4 mm DIA.)

10×1.5	11×1.5	12×1.75	14×2	16×2	10×0.75	10×1	10×1.25
11×0.75	11×1	11×1.25	12×0.75	12×1	12×1.25	12×1.5	14×1
14×1.25	14×1.5	16×1	16×1.5	18×1.5			

Additional parts:

T-Handle Tap Wrench.....M2-M5 × 80mm

Tap Wrenches.....190 mm, 380 mm

Die StocksFor 25.4 mm & 38.1 mm dies