



# Power Turtle X CPTX-T1-T7

1 x powerCON TRUE1 TOP In- 7 x powerCON® TRUE1® TOP Out - Indoor (IP20)

Power Turtle Xtreme Indoor (X) is a compact distribution solution for mobile applications. This distribution box is ideally suited for Indoor applications with restricted space / height and harsh usage conditions, for example in theaters, exhibition or similar applications. It also offers a very attractive price point.

## Features & Benefits

- |  |   |
|--|---|
| <ul style="list-style-type: none"><li>● Very compact, reduced height</li></ul>   | <ul style="list-style-type: none"><li>● Extreme robust and safe EASYLEN® housing with leather grain texture</li></ul> |
| <ul style="list-style-type: none"><li>● Highly reliable NEUTRIK® powerCON® TRUE1® TOP recepticals for In, Out and Daisy chaining</li></ul> | <ul style="list-style-type: none"><li>● Flame retardant (UL94-V2) and non-conductive housing material</li></ul>       |
| <ul style="list-style-type: none"><li>● High mechanical protection (high IK)</li></ul>   | <ul style="list-style-type: none"><li>● Light weight, and stackable housing design</li></ul>                          |
| <ul style="list-style-type: none"><li>● Versatile mounting options</li></ul>   | <ul style="list-style-type: none"><li>● Attractive price point</li></ul>  |

## Market & Application

- Markets. Professional video wall / lighting / audio
- Mobile application. Festivals, live events, exhibitions
- Semi-permanent applications. Theaters, studios

## Article order data

Article name	Details	Order code
CPTX-T1-T7	IN: powerCON® TRUE1® TOP OUT: 7x powerCON® TRUE1® TOP Indoor (IP20)	1035597

## Technical Information

### Product

Input device	1x powerCON® TRUE1® TOP
Output device	7x powerCON® TRUE1® TOP
Daisy chaining	1x powerCON® TRUE1® TOP

### Electrical

Contact resistance / protection class	Protection class II
Dielectric strength	0.5 kV / mm
Rated voltage	250V AC
Rated Current	16A (USA: 20A)
Number of electrical contacts	2 + PE
Phases	single-phase

### Mechanical

Lifetime	> 5000 mating cycles
Dimensions	220 x 150 x 65 mm
Conductor cross section	2,5 mm <sup>2</sup>
Weight	1.0 kg
Mounting options	Truss clamp, mounting wholes for pegging or suspension
Type of construction	Stackable

## Material

<b>Housing</b>	Easylen
<b>Color</b>	black

## Environmental

<b>Standards compatibility</b>	UL94-V2
<b>Protection class</b>	IP20
<b>Temperature range</b>	-25 °C to +70 °C