


ENERGIZER 319

ZEROMERCURY®

SILVER OXIDE



Industry Standard Dimensions




Specifications

Chemical System:	Silver Oxide (Zn/Ag ₂ O)
Nominal Voltage:	1.55 Volts
Typical Capacity:	22.5 mAh* (to 1.2 volts)
Capacity Test:	56K ohm continuous drain at 21°C
Typical Weight:	0.29 grams (0.011 oz.)
Typical Volume:	0.07 cubic centimeters (0.004 cubic inch)
Impedance (40 Hz):	50 to 60 ohms

* Varies according to the applied load, temperature, and cutoff voltage.


Cross Section



DESIGNED FOR USE ON CONTINUOUS LOW DRAIN

Typical Discharge Characteristics



Typical Performance at 21°C (70°F)



<u>Schedule</u>	<u>Typical Drains</u> at 1.55V (milliamperes)	<u>Load</u> (ohm)	<u>Cutoff</u> 1.2V (hours)
Continuous	0.028	56K	813

Temperature Characteristics

Typical Performance at Low Discharge Rates



Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.
Contents herein do not constitute a warranty and are for reference only.