


ENERGIZER 346

ZERO MERCURY

SILVER OXIDE



Industry Standard Dimensions




Specifications

Chemical System:	Silver Oxide (Zn/Ag ₂ O)
Nominal Voltage:	1.55 Volts
Typical Capacity:	9.5 mAh* (to 1.2 volts)
Capacity Test:	100K ohm continuous drain at 21°C
Typical Weight:	0.24 grams (0.008 oz.)
Typical Volume:	0.06 cubic centimeters (0.003 cubic inch)
Impedance (40 Hz):	30 to 40 ohms

* Varies according to the applied load, temperature, and cutoff voltage.

Cross Section




DESIGNED FOR USE ON CONTINUOUS LOW DRAIN

Typical Discharge Characteristics

Typical Performance at 21°C (70°F)

Schedule: Continuous
Typical Drain @1.55V:
 0.016 milliamperes
Load: 100K ohm




<u>Schedule</u>	<u>Typical Drains</u> at 1.55V (milliamperes)	<u>Load</u> (ohm)	<u>Cutoff</u> 1.2V (hours)
Continuous	0.016	100K	594


Temperature Characteristics

Typical Performance at Low Discharge Rates

Service Effects



Storage Effects



Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.
Contents herein do not constitute a warranty and are for reference only.