

Differential pressure gauge operated with smartphone

testo 510i

Compact professional measuring instrument from the Testo Smart Probes series, for use with smartphones/tablets

Measurement of gas flow and static pressure

Measurement menu for pressure-drop test incl. alarms

Measurement data analyzed and sent via testo Smart App

Magnetic fixture for better attachment

Space-saving and easy to transport



hPa

m/s



Bluetooth
+ App

testo Smart App
for free download




The differential pressure measuring instrument testo 510i, in combination with a smartphone or tablet, is suitable for the measurement of gas flow and static pressure, pressure drops on ventilators and filters as well as pressure drop measurement on gas pipes.

Via the testo Smart App installed on the end device, users can comfortably read off their measurement values and reliably determine timed and multi-point mean values. The App also includes a measurement menu for the pressure-drop test incl. alarm. All measurement data can be presented either as a diagram or in tabular form. The measurement protocols can then be directly sent as PDF or Excel files.

Technical data/accessories

testo 510i


testo 510i, differential pressure gauge operated with smartphone, incl. hose set (Ø 4 mm and 5 mm) with adapter, batteries and calibration protocol



Order no. 0560 1510

testo Smart App

The App turns your smartphone/tablet into the display of the testo 510i. The operation of the measuring instrument as well as the display of the measurement values take place by Bluetooth via the testo Smart App on your smartphone or tablet – independently of the measurement location. In addition to this, you can use the App to create measurement reports, add photos and comments to these, and send them by e-mail. For iOS and Android.



Sensor type	Pressure
Measuring range	-150 to 150 hPa
Accuracy ±1 digit	±0.05 hPa (0 to 1 hPa) ±(0.2 hPa + 1.5 % of m.v.) (1 to 150 hPa)
Resolution	0.01 hPa

General technical data

Compatability	requires iOS 11.0 or newer / Android 6.0 or newer requires mobile end device with Bluetooth 4.0
Storage temperature	-20 to +60 °C
Operating temperature	-20 to +50 °C
Battery type	3 micro batteries AAA
Battery life	150 hrs
Dimensions	148 x 36 x 23 mm

1981 1744/msp/dk/08.2021

Subject to change without notice.

Accessories	Order no.
testo Smart Case (VAC) for the storage and transport of testo 405i, testo 410i, testo 510i, testo 605i, testo 805i and testo 905i, dimensions 270 x 190 x 60 mm	0516 0260
ISO calibration certificate pressure, accuracy > 0.6 % of final value	0520 0005

