

VOLTCRAFT

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.



VC-12668692 RECHARGEABLE BATTERY

Item no. 3324602

The rechargeable batteries are lead-lead dioxide systems. The dilute sulfuric acid electrolyte is absorbed by separators and plates and thus immobilized. Should the battery be accidentally overcharged producing hydrogen and oxygen, special oneway valves allow the gases to escape thus avoiding excessive pressure build-up. Otherwise, the battery is completely sealed and is, therefore, maintenance-free, leak proof and usable in any position.


FEATURES

Positive and negative plates in lead-calcium-tin alloy // Stable Quality & High Reliability // Sealed Construction // Long Service Life // Maintenance-Free Operation // Low Pressure Venting System // Low Self Discharge // U.L. Component // Recognition // Six months shelf life at 20 °C // Design life 10 years



Battery Construction

Component	Positive plate	Negative plate	Container	Cover	Safety valve	Terminal	Separator	Electrolyte
Raw material	Lead dioxide	Lead	ABS	ABS	Rubber	Pb	Fiberglass	Sulfuric acid



DIMENSIONS & WEIGHT

Length (mm):	195
Width (mm):	130
Height (mm):	155
Total Height (mm):	168
Approx. Weight (Kg)*:	11.0

*Weight deviation: $\pm 3\%$

Battery Specification

Performance Characteristics	
Nominal Voltage	12V
Number of cell	6
Design Life	10years
Nominal Capacity (25°C)	
10 hour rate (3.30A, 10.8V)	33.0Ah
5 hour rate (5.58A, 10.5V)	27.9Ah
1 hour rate (22.3A, 9.6V)	22.3Ah
Internal Resistance	
Fully Charged battery 77°F(25°C)	≤10 mOhms
Self-Discharge	
3% of capacity declined per month at 20°C(average)	
Operating Temperature Range	
Discharge	-20~60°C
Charge	-10~60°C
Storage	-20~60°C
Max. Discharge Current (25°C)	330A(5s)
Short Circuit Current	850A
Charge Methods: Constant Voltage Charge (25°C)	
Cycle use	2.4-2.45VPC
Maximum charging current	9.9A
Temperature compensation	-30mV/°C
Standby use	2.20-2.30VPC
Temperature compensation	-20mV/°C

Discharge Constant Current (Amperes at 25° C)

End Point								
Volts/Cell	10min	15min	30min	45min	1h	3h	5h	10h
1.60V	80.2	61.5	37.0	26.9	22.3	9.08	6.30	3.36
1.65V	77.3	59.4	36.3	26.9	21.9	8.97	6.25	3.35
1.70V	73.0	54.5	33.2	25.2	21.2	8.45	6.15	3.32
1.75V	69.0	52.0	32.8	24.5	20.3	8.25	5.58	3.31
1.80V	60.0	49.5	31.9	23.8	19.8	8.18	5.50	3.30

Discharge Constant Power (Watts at 25° C)

End Point								
Volts/Cell	10min	15min	30min	45min	1h	2h	3h	5h
1.60V	150	117	72.4	53.8	40.9	23.3	17.4	12.2
1.65V	145	110	69.3	53.2	40.5	23.1	17.3	11.9
1.70V	136	107	64.5	51.2	39.9	22.6	16.8	11.5
1.75V	132	103	62.7	49.1	39.1	21.8	16.0	11.3
1.80V	116	97.9	61.0	48.8	38.3	21.0	15.2	11.0

(Note) The above characteristics data are average values obtained within three charge/discharge cycles, not the minimum values. All data shall be changed without notice. Vision reserves the right to explain and update the information contained hereinto.

