

VOLTCRAFT

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

VC-12668696 LEAD BATTERY MAINTENANCE-FREE 12 V 65 AH



Item no. 3324606

The rechargeable battery is a lead-lead dioxide system. The dilute sulfuric acid electrolyte is absorbed by the separators and plates and is thus immobilized. Should the battery be accidentally overcharged, producing hydrogen and oxygen, special one-way valves allow the gases to escape, thus avoiding excessive pressure build-up. Otherwise, the battery is completely sealed and is, therefore, maintenance-free, leak-proof, and usable in any position.

FEATURES

Positive and negative plates in lead-calcium-tin alloy // Stable quality & high reliability // Sealed construction // Long service life // Maintenance-free operation // Low pressure venting system // Low self-discharge // U.L. Component recognition // Six-month shelf life at 20 °C // 10-year design life



TECHNICAL DATA

Battery Construction


Component	Raw material
Positive plate	Lead dioxide
Negative plate	Lead
Container	ABS
Cover	ABS
Safety valve	Rubber
Terminal	Copper
Separator	Fiberglass
Electrolyte	Sulfuric acid

Dimensions & Weight

Product dimension (L x W x H)	350 x 167 x 179 mm
Total height	179 mm
Weight	approx. 23.4 kg (± 3%)

Performance Characteristics

Nominal voltage	12 V
Number of cell	6 pcs
Design life	10 years
Nominal capacity (25 °C)	10 hour rate (6.5 A, 10.8 V): 65.0 Ah 5 hour rate (11.3 A, 10.5 V): 56.5 Ah 1 hour rate (44.2 A, 9.6 V): 44.2 Ah
Internal resistance of fully charged battery (25 °C)	≤6.8 mOhms
Self-discharge (20 °C)	3% of capacity declined per month (average)
Operating temperature	Discharge: -20 to 60 °C Charge: -10 to 60 °C Storage: -20 to 60 °C
Max. discharge current (25 °C)	650 A (5s)
Short circuit current	1700 A
Charge methods	Constant voltage charge (25 °C)
Cycle use	14.4 - 14.7 V
Maximum charging current	19.5 A
Temperature compensation	-30 mV/°C
Standby use	13.2 - 13.8 V
Temperature compensation	-20 mV/°C



Discharge Constant Current (Amperes at 25 °C)

End Point Volts/Cell	10 min	15 min	30 min	45 min	1 h	3 h	5 h	10 h
1.60 V	160	125	70.5	53.0	44.2	17.7	12.1	7.01
1.65 V	151	116	68	52.8	41.9	17.1	11.7	6.90
1.70 V	143	114	66.3	50.1	41.5	16.9	11.5	6.76
1.75 V	132	108	66.2	49.8	40.9	16.7	11.3	6.61
1.80 V	120	100	61.8	47.3	38.3	16.3	11.1	6.50

Discharge Constant Power (Watts at 25 °C)

End Point Volts/Cell	10 min	15 min	30 min	45 min	1 h	2 h	3 h	5 h
1.60 V	282	222	132	98.0	80.8	46.1	34.5	22.8
1.65 V	267	206	127	96.5	79.0	45.1	33.8	22.6
1.70 V	252	197	118	94.5	77.2	44.6	33.7	22.4
1.75 V	237	193	116	92.4	75.4	43.2	32.4	22.0
1.80 V	220	183	114	91.2	75.0	42.5	31.7	21.7

Note: The above characteristics data are average values obtained over three charge/discharge cycles, not the minimum values. All data are subject to change without notice. The manufacturer reserves the right to clarify and update the information contained herein.

