

VOLTCRAFT - TOP PERFORMANCE IN EVERY WAY

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

VC-41 Socket Tester



Item no: 3208233

The product is a multifunction socket tester. The product is intended to:

Measure AC voltage between Line-Neutral (L-N) and Line-Earth (L-E). //

Test Residual Current Devices (RCD) wired to sockets. //

Detect nearby AC voltage using Non-Contact Voltage (NCV).

The product is intended for use within the specifications of measuring category CAT II.



The product must only be used by persons capable of correctly setting up test scenarios and interpreting test results.

The accompanying mobile app can be used to control the product remotely via Bluetooth. The user must always ensure that the given testing environment is safe for remote controlling.

TECHNICAL DATA

Batteries	2x 1.5 V AAA
Rated input	100 - 250 V/AC, 50/60 Hz, < 0.1 A
Measurable voltage	100 - 250 V/AC
Overvoltage category	CAT II
Dual voltage support	110/220 V/AC
Measurable frequency	40 - 70 Hz
Operating current	max. 25 mA
Mobile app name	Voltcraft VC-41
Wireless connectivity	Bluetooth BLE4.0
Wireless frequency	2402 - 2480 MHz
Wireless transmission power	-6 dBm < PAV < 4 dBm
Operation temperature	-10 to +50 °C
Operating humidity	<80 % RH
Storage temperature	-10 to +50 °C
Storage humidity	<80 % RH
Product size	74 x 67 x 81.5 mm
Product weight	approx 136 g (without battery)

FEATURES

USB-C® and USB-A // 20 V/DC, max. 45 W // Overload and short-circuit protection

CONTENTS

Product // 2x AAA batteries // Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method (e.g. photocopying, microfilming or the capture in electronic data processing systems) requires prior written approval from the editor. Reprinting, also in part, is prohibited. This publication reflects the technical status at the time of printing.

Copyright by Conrad Electronic SE.

*3208233_V1_0525_en_ds 9007201401581323 I2/O1 en