Heat-Shrink-Tube Reels 2:1

Item-No.: 24CA261 … 24CA281, 25CA582 … 25CA623

RoHS Pb
+125 °C
-40 °C
15 kV/mm

These high-quality shrink sleeves are particularly suitable for service workshops, electronics technicians and applications with a high demand for shrink tubing. The heat-shrink tube is wound onto a cardboard reel and can therefore be cut to length individually. Various available nominal diameters open up a wide range of applications. The standard version with a shrink ratio of 2:1 without internal adhesive is ideal for most applications.

Technical Specifications

Material: PE • Shrink ratio: 2:1 • Shrink temperature (min.): 90 °C • Shrink temperature (max.): 125 °C • Operating temperature: -40 °C … +125 °C • Tensile strength (min.): 10.4 MPa • Dielectric strength 15 kV/mm (30 s.) • Rated voltage: 600 V • Elongation break: min. 300% • Colors: Black, White, Transparent • Selling unit: Reel or per m.

Item-No.	Description	Diameter	Wall thickness material	Wall thickness shrinked	Content	EAN/GTIN
24CA261	Shrinking tube 2:1 black Φ 1 mm	1 mm	0.16 (±0.02) mm	0.32 (±0.04) mm	200 m	4260732287001
24CA262	Shrinking tube 2:1 black Φ 2 mm	2 mm	0.18 (±0.02) mm	0.36 (±0.04) mm	200 m	4260732287018
24CA263	Shrinking tube 2:1 black Φ 4 mm	4 mm	0.19 (±0.02) mm	0.38 (±0.04) mm	200 m	4260732287025
24CA264	Shrinking tube 2:1 black Φ 6 mm	6 mm	0.21 (±0.02) mm	0.42 (±0.04) mm	100 m	4260732287032
24CA265	Shrinking tube 2:1 black Φ 8 mm	8 mm	0.21 (±0.02) mm	0.42 (±0.04) mm	100 m	4260732287049
24CA266	Shrinking tube 2:1 black Φ 10 mm	10 mm	0.22 (±0.02) mm	0.44 (±0.04) mm	100 m	4260732287056
24CA267	Shrinking tube 2:1 black Φ 12 mm	12 mm	0.23 (±0.02) mm	0.46 (±0.04) mm	100 m	4260732287063
24CA268	Shrinking tube 2:1 black Φ 14 mm	14 mm	0.23 (±0.02) mm	0.46 (±0.04) mm	100 m	4260732287070
24CA269	Shrinking tube 2:1 black Φ 16 mm	16 mm	0.24 (±0.02) mm	0.48 (±0.04) mm	100 m	4260732287087
24CA270	Shrinking tube 2:1 black Φ 18 mm	18 mm	0.24 (±0.02) mm	0.48 (±0.04) mm	50 m	4260732287094
24CA271	Shrinking tube 2:1 black Φ 20 mm	20 mm	0.25 (±0.02) mm	0.5 (±0.04) mm	50 m	4260732287100
24CA272	Shrinking tube 2:1 black Φ 25 mm	25 mm	0.27 (±0.03) mm	0.54 (±0.06) mm	50 m	4260732287117
24CA273	Shrinking tube 2:1 black Φ 30 mm	30 mm	0.28 (±0.03) mm	0.56 (±0.06) mm	25 m	4260732287124
24CA274	Shrinking tube 2:1 black Φ 35 mm	35 mm	0.29 (±0.03) mm	0.58 (±0.06) mm	25 m	4260732287131
24CA275	Shrinking tube 2:1 black Φ 40 mm	40 mm	0.3 (±0.03) mm	0.6 (±0.06) mm	25 m	4260732287148
24CA276	Shrinking tube 2:1 black Φ 50 mm	50 mm	0.33 (±0.03) mm	0.66 (±0.06) mm	25 m	4260732287155
24CA277	Shrinking tube 2:1 black Φ 60 mm	60 mm	0.35 (±0.03) mm	0.7 (±0.06) mm	25 m	4260732287162
24CA278	Shrinking tube 2:1 black Φ 70 mm	70 mm	0.38 (±0.03) mm	0.76 (±0.06) mm	25 m	4260732287179
24CA279	Shrinking tube 2:1 black Φ 80 mm	80 mm	0.4 (±0.03) mm	0.8 (±0.06) mm	25 m	4260732287186
24CA280	Shrinking tube 2:1 black Φ 90 mm	90 mm	0.45 (±0.03) mm	0.9 (±0.06) mm	25 m	4260732287193
24CA281	Shrinking tube 2:1 black Φ 100 mm	100 mm	0.49 (±0.03) mm	0.89 (±0.06) mm	25 m	4260732287209
25CA582	Shrinking tube 2:1 white Φ 1 mm roll 200 m	1 mm	0.16 (±0.02) mm	0.32 (±0.04) mm	200 m	4262511622287
25CA583	Shrinking tube 2:1 white Φ 2 mm roll 200 m	2 mm	0.18 (±0.02) mm	0.36 (±0.04) mm	200 m	4262511622294
25CA584	Shrinking tube 2:1 white Φ 4 mm roll 200 m	4 mm	0.19 (±0.02) mm	0.38 (±0.04) mm	200 m	4262511622300
25CA586	Shrinking tube 2:1 white Φ 8 mm roll 100 m	8 mm	0.21 (±0.02) mm	0.42 (±0.04) mm	100 m	4262511622324
25CA587	Shrinking tube 2:1 white Φ 10 mm roll 100 m	10 mm	0.22 (±0.02) mm	0.44 (±0.04) mm	100 m	4262511622331
25CA588	Shrinking tube 2:1 white Φ 12 mm roll 100 m	12 mm	0.23 (±0.02) mm	0.46 (±0.04) mm	100 m	4262511622348

Continue next page

This is a publication by Quadrios GmbH • Bahnhofstraße 16 • D-92670 Windischeschenbach (www.quadrios.de)
All right including translation reserved. Reproduction by any method or the capture in electronic data processing system require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.
All statements without guarantee
© Quadrios GmbH
Version 2025/09

QUADRIOS

TECHNICAL DATA SHEET

www.quadrios.de

Item-No.	Description	Diameter	Wall thickness material	Wall thickness shrinked	Content	EAN/GTIN
25CA589	Shrinking tube 2:1 white Φ 14 mm roll 100 m	14 mm	0.23 (±0.02) mm	0.46 (±0.04) mm	100 m	4262511622355
25CA590	Shrinking tube 2:1 white Φ 16 mm roll 100 m	16 mm	0.24 (±0.02) mm	0.48 (±0.04) mm	100 m	4262511622362
25CA591	Shrinking tube 2:1 white Φ 18 mm roll 50 m	18 mm	0.24 (±0.02) mm	0.48 (±0.04) mm	50 m	4262511622379
25CA592	Shrinking tube 2:1 white Φ 20 mm roll 50 m	20 mm	0.25 (±0.02) mm	0.5 (±0.04) mm	50 m	4262511622386
25CA593	Shrinking tube 2:1 white Φ 25 mm roll 50 m	25 mm	0.27 (±0.03) mm	0.54 (±0.06) mm	50 m	4262511622393
25CA594	Shrinking tube 2:1 white Φ 30 mm roll 25 m	30 mm	0.28 (±0.03) mm	0.56 (±0.06) mm	25 m	4262511622409
25CA595	Shrinking tube 2:1 white Φ 35 mm roll 25 m	35 mm	0.29 (±0.03) mm	0.58 (±0.06) mm	25 m	4262511622416
25CA596	Shrinking tube 2:1 white Φ 40 mm roll 25 m	40 mm	0.3 (±0.03) mm	0.6 (±0.06) mm	25 m	4262511622423
25CA597	Shrinking tube 2:1 white Φ 50 mm roll 25 m	50 mm	0.33 (±0.03) mm	0.66 (±0.06) mm	25 m	4262511622430
25CA598	Shrinking tube 2:1 white Φ 60 mm roll 25 m	60 mm	0.35 (±0.03) mm	0.7 (±0.06) mm	25 m	4262511622447
25CA599	Shrinking tube 2:1 white Φ 70 mm roll 25 m	70 mm	0.38 (±0.03) mm	0.76 (±0.06) mm	25 m	4262511622454
25CA600	Shrinking tube 2:1 white Φ 80 mm roll 25 m	80 mm	0.4 (±0.03) mm	0.8 (±0.06) mm	25 m	4262511622461
25CA601	Shrinking tube 2:1 white Φ 90 mm roll 25 m	90 mm	0.45 (±0.03) mm	0.9 (±0.06) mm	25 m	4262511622478
25CA602	Shrinking tube 2:1 white Φ 100 mm roll 25 m	100 mm	0.49 (±0.03) mm	0.89 (±0.06) mm	25 m	4262511622485
25CA603	Shrinking tube 2:1 transparent Φ 1 mm roll 200 m	1 mm	0.16 (±0.02) mm	0.32 (±0.04) mm	200 m	4262511622492
25CA604	Shrinking tube 2:1 transparent Φ 2 mm roll 200 m	2 mm	0.18 (±0.02) mm	0.36 (±0.04) mm	200 m	4262511622508
25CA605	Shrinking tube 2:1 transparent Φ 4 mm roll 200 m	4 mm	0.19 (±0.02) mm	0.38 (±0.04) mm	200 m	4262511622515
25CA606	Shrinking tube 2:1 transparent Φ 6 mm roll 100 m	6 mm	0.21 (±0.02) mm	0.42 (±0.04) mm	100 m	4262511622522
25CA607	Shrinking tube 2:1 transparent Φ 8 mm roll 100 m	8 mm	0.21 (±0.02) mm	0.42 (±0.04) mm	100 m	4262511622539
25CA608	Shrinking tube 2:1 transparent Φ 10 mm roll 100 m	10 mm	0.22 (±0.02) mm	0.44 (±0.04) mm	100 m	4262511622546
25CA609	Shrinking tube 2:1 transparent Φ 12 mm roll 100 m	12 mm	0.23 (±0.02) mm	0.46 (±0.04) mm	100 m	4262511622553
25CA610	Shrinking tube 2:1 transparent Φ 14 mm roll 100 m	14 mm	0.23 (±0.02) mm	0.46 (±0.04) mm	100 m	4262511622560
25CA611	Shrinking tube 2:1 transparent Φ 16 mm roll 100 m	16 mm	0.24 (±0.02) mm	0.48 (±0.04) mm	100 m	4262511622577
25CA612	Shrinking tube 2:1 transparent Φ 18 mm roll 50 m	18 mm	0.24 (±0.02) mm	0.48 (±0.04) mm	50 m	4262511622584
25CA613	Shrinking tube 2:1 transparent Φ 20 mm roll 50 m	20 mm	0.25 (±0.02) mm	0.5 (±0.04) mm	50 m	4262511622591
25CA614	Shrinking tube 2:1 transparent Φ 25 mm roll 50 m	25 mm	0.27 (±0.03) mm	0.54 (±0.06) mm	50 m	4262511622607
25CA615	Shrinking tube 2:1 transparent Φ 30 mm roll 25 m	30 mm	0.28 (±0.03) mm	0.56 (±0.06) mm	25 m	4262511622614
25CA616	Shrinking tube 2:1 transparent Φ 35 mm roll 25 m	35 mm	0.29 (±0.03) mm	0.58 (±0.06) mm	25 m	4262511622621
25CA617	Shrinking tube 2:1 transparent Φ 40 mm roll 25 m	40 mm	0.3 (±0.03) mm	0.6 (±0.06) mm	25 m	4262511622638
25CA618	Shrinking tube 2:1 transparent Φ 50 mm roll 25 m	50 mm	0.33 (±0.03) mm	0.66 (±0.06) mm	25 m	4262511622645
25CA619	Shrinking tube 2:1 transparent Φ 60 mm roll 25 m	60 mm	0.35 (±0.03) mm	0.7 (±0.06) mm	25 m	4262511622652
25CA620	Shrinking tube 2:1 transparent Φ 70 mm roll 25 m	70 mm	0.38 (±0.03) mm	0.76 (±0.06) mm	25 m	4262511622669
25CA621	Shrinking tube 2:1 transparent Φ 80 mm roll 25 m	80 mm	0.4 (±0.03) mm	0.8 (±0.06) mm	25 m	4262511622676
25CA622	Shrinking tube 2:1 transparent Φ 90 mm roll 25 m	90 mm	0.45 (±0.03) mm	0.9 (±0.06) mm	25 m	4262511622683
25CA623	Shrinking tube 2:1 transparent Φ 100 mm roll 25 m	100 mm	0.49 (±0.03) mm	0.89 (±0.06) mm	25 m	4262511622690

This is a publication by Quadrios GmbH • Bahnhofstraße 16 • D-92670 Windischeschenbach (www.quadrios.de)

All right including translation reserved. Reproduction by any method or the capture in electronic data processing system require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

All statements without guarantee

© Quadrios GmbH

Version 2025/09