


CDX1-1748




- 1,600Hz recommended min. crossover freq (12dB/oct)
- Single piece polyimide diaphragm and surround
- Sound Castle soft clamping diaphragm assembly
- Screw fitting

Frequency Response and Impedance Curves



Measured - Plane Wave Tube



Measured - Exponential Horn 90° x 40° radiation pattern

Power rating: Tested for two hours on plane wave tube using a continuous, band-limited pink noise signal as per AES standard. Power calculated on minimum impedance.

Continuous power rating: Defined as 3dB greater than the AES rating.

Sensitivity: Measured on axis at 1W, 1m, using typical horn, in 2 anechoic environment.

General Specifications

Power Rating	60W
Continuous power rating	120W
Rated impedance	8
Sensitivity	110dB
Frequency range	1000-20,000Hz
Recommended min. crossover	1600Hz
r (12dB/oct)	
Magnet type	Ferrite
Voice coil diameter	44mm / 1.75in
Voice coil material	Edgewound copper clad aluminium
Diaphragm material	Polyimide
Surround material	Polyimide

Mounting Information

Width	120mm / 4.7in
Depth	53mm / 2.1in
Fitting	Screw (35mm/1.38in diameter)
Bolt version	CDX1-1747
Throat exit	25mm / 1in
Unit weight	2.3kg / 5.1lb

Packed Dimensions & Weight

Single pack size W x D x H	140mm x 170mm x 70mm / 5.5in x 6.7in x 2.8in
Single pack weight	3kg / 6.6lb
Multi pack qty	6
Multi pack size W x D x H	430mm x 370mm x 90mm / 16.9in x 14.6in x 3.5in
Multi pack weight	14kg / 30.8lb