



Heat-Shrink-Tube Reels 4:1 Item-No.: 24CA296 ... 24CA305



These high-quality shrink sleeves are particularly suitable for service workshops, electronics technicians and applications with a high demand for shrink tubing. The black heat-shrink tube is wound onto a cardboard reel and can therefore be cut to length individually. Various available nominal diameters open up a wide range of applications. The version with inner glue and a very high shrink ratio of 4:1 is ideal for applications with high demands on the wrapping.

Technical Specifications

Material: PE • Shrink ratio: 4:1 • Hot melt adhesive • Shrink temperature (min.): 80 °C • Shrink temperature (max.): 125 °C • Operating temperature: -40 °C ... +125 °C • Double-wall-technology • Tensile strength (min.): 10.4 MPa • Dielectric strength 15 kV/mm (30 sec.) • Rated voltage: 600 V • Axial shrinkage: <8% • Color: Black.

Item-No.	Description	Diameter	Total wall thickness	Content	EAN/GTIN
24CA296	Shrinking tube with glue 4:1 black Ø 4 mm	4 mm	1.05 (±0.15) mm	200 m	4260732287353
24CA297	Shrinking tube with glue 4:1 black Ø 6 mm	6 mm	1.15 (±0.15) mm	100 m	4260732287360
24CA298	Shrinking tube with glue 4:1 black Ø 8 mm	8 mm	1.55 (±0.15) mm	100 m	4260732287377
24CA299	Shrinking tube with glue 4:1 black Ø 12 mm	12 mm	1.75 (±0.3) mm	50 m	4260732287384
24CA300	Shrinking tube with glue 4:1 black Ø 16 mm	16 mm	2,0 (±0.3) mm	50 m	4260732287391
24CA301	Shrinking tube with glue 4:1 black Ø 20 mm	20 mm	2.4 (±0.4) mm	50 m	4260732287407
24CA302	Shrinking tube with glue 4:1 black Ø 24 mm	24 mm	2.6 (±0.4) mm	50 m	4260732287414
24CA303	Shrinking tube with glue 4:1 black Ø 32 mm	32 mm	3,0 (±0.5) mm	25 m	4260732287421
24CA304	Shrinking tube with glue 4:1 black Ø 40 mm	40 mm	3.1 (±0.5) mm	25 m	4260732287438
24CA305	Shrinking tube with glue 4:1 black Ø 52 mm	52 mm	3.35 (±0.5) mm	25 m	4260732287445