


12DPW4_1.5 series

12W - Single/Dual Output - Wide Input - Isolated & Regulated DC-DC Converter



- ⊕ Wide 4:1 input voltage range
- ⊕ Input/Output Isolation
Voltage: 1.5kVDC
- ⊕ Operating Temperature
Range: -40°C to +85°C
- ⊕ Short circuit protection (SCP)
- ⊕ Remote On/Off

- ⊕ High efficiency
- ⊕ 12W DIL package
- ⊕ Meet EN55022, Class A (Radiation)
- ⊕ Shielded Metal Case with Insulated Baseplate
- ⊕ Lead Free Design, RoHS Compliant
- ⊕ 24pin DIP Package with Industry-Standard Footprint
- ⊕ Customer Design Available



Common specifications

Short circuit protection:	Continuous, automatic recovery
Cooling:	Free air convection
Operation temperature range:	-40°C~+85°C
Storage temperature range:	-55°C~+125°C
Maximum case temperature:	100°C
Switching frequency:	400kHz TYP
Storage humidity range:	95% MAX
Radiated emissions:	EN55022/Class A
Conducted emissions:	EN55022/Class A
Case material:	Five-Side Shielded Case
Potting material:	Epoxy (UL94V-0)
MTBF (MIL-HDBK-217F @25°C):	900,000 hours
Weight:	17.5g

Input specifications

Item	Test condition	Min	Typ	Max	Units
Input filter	Pi Type				
Protection	Fuse recommended				
Input surge voltage (100ms max.)	- Nominal input (12V) - Nominal input (24V) - Nominal input (48V)		25 50 100		VDC
Input reflected ripple current	Nominal Vin and full load		50		mAp-p
Start-up time	Nominal Vin and constant resistive load		500		ms
Remote ON/OFF	- Converter: ON - Converter: OFF		Open or 3.5V<Vr<12V Short or 0V<Vr<1.2V		
Sourcing current of remote control pin	Nominal Vin		<0.2		mA
Idle input current (at Remote OFF state)	Nominal Vin		<2.5		mA

DC-DC Converter

12 Watt

The 12DPW4_1.5 series are isolated 12W DC-DC converters. Designed with high efficiency, they allow the operating temperature range of these units to be -40°C to +85°C in a 24 pin DIP package with industry-standard footprint. Further features include wide 2:1 input voltage range, remote on/off control, short-circuit protection and over voltage protection.

These converters are well suitable for battery operated equipment, measurement equipment, telecom, wireless network and industry control systems. Everywhere where isolated, tightly regulated voltages and compact size are required.

Output specifications

Item	Test condition	Min	Typ	Max	Units
Output power				12	W
Minimum load	10% of full load				
Output voltage accuracy	Full load and nominal Vin			±2	%
Overload protection			150		%
Line regulation	High Line to Low Line		±0.5		%
Load regulation	Single & Dual (F.L-25%F.L)		±0.5		%
Ripple and noise	20MHz Bandwidth			100	mVp-p
Transient response settling time	50% load step change		350		µs

Isolation specifications

Item	Test condition	Min	Typ	Max	Units
Isolation voltage	Input to output	1500			VDC
Isolation resistance	Test at 500VDC	1000			MΩ

Example:

12DPW4_2415S1.5

12 = 12Watt; D = DIP; P = series; W4 = wide input (4:1) 9-36Vin; 15Vout; S = single output; 1.5 = 1500VDC isolation

Note:

- Only typical model listed. Non-standard models will be different from the above, please contact us for more details.
- All specifications are typical at nominal input, full load and 25°C unless otherwise stated.
- In this datasheet, all the test methods of indications are based on corporate standards.


12DPW4_1.5 series

12W - Single/Dual Output - Wide Input - Isolated & Regulated
DC-DC Converter


Part Number	Input Voltage [VDC] Range	Input Current [mA] No load	Input Current [mA] Full load	Output Voltage [VDC]	Output Current [mA] Full load	Efficiency [% Typ.]
12DPW4_2403S1.5	9-36	30	602	3.3	3500	80
12DPW4_2405S1.5	9-36	30	610	5	2400	82
12DPW4_2412S1.5	9-36	30	602	12	1000	83
12DPW4_2415S1.5	9-36	30	602	15	800	83
12DPW4_4803S1.5	18-75	30	301	3.3	3500	80
12DPW4_4805S1.5	18-75	30	305	5	2400	82
12DPW4_4812S1.5	18-75	30	301	12	1000	83
12DPW4_4815S1.5	18-75	30	301	15	800	83
12DPW4_2405D1.5	9-36	30	602	±5	±1200	83
12DPW4_2412D1.5	9-36	30	602	±12	±500	83
12DPW4_2415D1.5	9-36	30	602	±15	±400	83
12DPW4_4805D1.5	18-75	30	301	±5	±1200	83
12DPW4_4812D1.5	18-75	30	301	±12	±500	83
12DPW4_4815D1.5	18-75	30	301	±15	±400	83

Typical characteristics



Temperature derating graph



Tolerance envelope graph




Recommended test circuit



12DPW4_1.5 series


12W - Single/Dual Output - Wide Input - Isolated & Regulated
DC-DC Converter

External filter



Input filter components (C1, C2, L) are used to help meet conducted emissions (EN55022 class A) requirement for the module. These components should be mounted as close as possible to the module; and all leads should be minimized to decrease radiated noise.

Mechanical dimensions



Note:
Unit: mm[inch]
Tolerances: $\pm 0.5\text{mm}$ [$\pm 0.02\text{inch}$]
Pin size tolerance: $0.6\phi \pm 0.05\text{mm}$

PIN connection							
PIN	1	2, 3	9	11	14	16	22, 23
Single	Remote on/off	-Vin	NC	NC	+Vout	-Vout	+Vin
Dual	Remote on/off	-Vin	Common	-Vout	+Vout	Common	+Vin