

1T8A2_3UP series

1W - Single Output DC-DC Converter - Fixed Input - Isolated & Unregulated



DC-DC Converter

1 Watt

- ⊕ 8PIN SMD Package
- ⊕ No load input current as low as 5 mA
- ⊕ Continuous short circuit protection
- ⊕ High Efficiency up to 87%
- ⊕ Unregulated Output Types
- ⊕ 3kVDC Isolation
- ⊕ Operating Temperature: -40°C to +105°C
- ⊕ Industry Standard Pinout
- ⊕ IEC62368, UL62368, EN62368

The 1T8A2_3UP series is specially designed for applications where a group of polar power supplies are isolated from the input power supply in a distributed power supply system on a circuit board.

These products apply to:

- 1) Where the voltage of the input power supply is fixed (voltage variation $\leq \pm 10\%$)
- 2) Where isolation is necessary between input and output (isolation voltage $\leq 3000\text{VDC}$)
- 3) Where the regulation of the output voltage and the output ripple noise are not demanding. Such as: digit circuit condition; normal low-frequency artificial circuit condition; relay drive circuit condition, etc.



Common specifications

Short circuit protection:	continuous
Operation temperature range:	-40°C ~ +105°C
Storage temperature range:	-55°C ~ +125°C
Storage humidity range:	< 95% (Non Condensing)
MTBF (MIL-HDBK-217F@25°C):	>3,500,000 hours
Case material:	DAP
Cooling:	Free air convection
Dimensions:	12.7 x 7.6 x 6.25 mm
Weight:	1.2 g

Input specifications

Item	Test condition	Min	Typ	Max	Units
Voltage range (Vo, Io Nom)	Vin: 3.3V, 5V Vin: 9V, 12V, 15V, 24V			±10 ±20	% %
Filter	Capacitor				

Isolation specifications

Item	Test condition	Min	Typ	Max	Units
Isolation voltage	Input to output	3000			VDC
Isolation resistance	Test at 500VDC	1000			MΩ
Isolation capacitance	Input-output, 100KHz/0.1V		20		pF

EMC specifications

Emissions	CE	CISPR32/EN55032 CLASS B (see Fig. 1 for recommended circuit)
Emissions	RE	CISPR32/EN55032 CLASS B (see Fig. 1 for recommended circuit)
Immunity	ESD	IEC/EN61000-4-2 Air ±8kV, Contact ±4kV perf. Criteria B

Output specifications

Item	Test condition	Min	Typ	Max	Units
Voltage tolerance	100% full load			±5	%
Line regulation	For Vin change of 1%		±1.2		%
Load regulation	• 3.3V (10% To 100% F.L) • 5V (10% To 100% F.L) • 9V (10% To 100% F.L) • 12V (10% To 100% F.L) • 15V (10% To 100% F.L)		15 10 8 7 6	20 15 10 10 10	% % % % %
Ripple & Noise* (BW = DC To 20MHz)	• Vo: 3.3V, 5V, 9V, 12V, 15V		30	75	mVp-p
Switching frequency (Full load, nominal input)	• 3.3V, 5V Vin • Other Vin		215/370 250		KHz KHz

* Ripple and noise tested with "parallel cable" method. See detailed operation instructions at DC-DC Application Notes.

Example:

1T8A2_1205S3UP

1 = 1Watt; T8 = SMT8; A2 = Series; 12 = 12Vin; 05 = 5Vout;
S = Single output; 1.5 = 3kVDC isolation; U = Unregulated output;
P = Short circuit protection (SCP)

Note:

1. Operation under minimum load will not damage the converter; However, they may not meet all specification listed.
2. Max. Capacitive Load tested at input voltage range and full load.
3. All specifications measured at Ta = 25°C, humidity < 75%, nominal input voltage and rated output load unless otherwise specified.
4. In this datasheet, all the test methods of indications are based on our corporate standards.



1T8A2_3UP series

1W - Single Output DC-DC Converter - Fixed Input - Isolated & Unregulated

Product Selection Guide

Part Number	Output Voltage [VDC]	Output Current [mA]	Efficiency [%, typ]	Capacitive Load [μF]
1T8A2_0303S3UP	3.3	303	76	2400
1T8A2_0305S3UP	5	200	82	2400
1T8A2_0309S3UP	9	112	83	1000
1T8A2_0312S3UP	12	84	84	470
1T8A2_0315S3UP	15	67	84	330
1T8A2_0503S3UP	3.3	303	76	2400
1T8A2_0505S3UP	5	200	82	2400
1T8A2_0509S3UP	9	112	83	1000
1T8A2_0512S3UP	12	84	84	470
1T8A2_0515S3UP	15	67	84	330
1T8A2_0903S3UP	3.3	303	76	2400
1T8A2_0905S3UP	5	200	82	2400
1T8A2_0909S3UP	9	112	83	1000
1T8A2_0912S3UP	12	84	84	470
1T8A2_0915S3UP	15	67	84	330
1T8A2_1203S3UP	3.3	303	78	2400
1T8A2_1205S3UP	5	200	82	2400
1T8A2_1209S3UP	9	112	85	1000
1T8A2_1212S3UP	12	84	85	680
1T8A2_1215S3UP	15	67	87	330
1T8A2_1503S3UP	3.3	303	78	2400
1T8A2_1505S3UP	5	200	82	2400
1T8A2_1509S3UP	9	112	85	1000
1T8A2_1512S3UP	12	84	85	680
1T8A2_1515S3UP	15	67	87	330
1T8A2_2403S3UP	3.3	303	78	2400
1T8A2_2405S3UP	5	200	82	2400
1T8A2_2409S3UP	9	112	85	1000
1T8A2_2412S3UP	12	84	85	680
1T8A2_2415S3UP	15	67	87	330


Typical characteristics



1T8A2_3UP series


1W - Single Output DC-DC Converter - Fixed Input - Isolated & Unregulated

Recommended test circuit




Vin	Cin	Single Vout	Cout
3.3VDC	4.7μF/25V	3.3VDC	10μF/16V
5VDC	4.7μF/25V	5VDC	10μF/16V
9VDC	4.7μF/25V	9VDC	2.2μF/16V
12VDC	2.2μF/25V	12VDC	2.2μF/25V
15VDC	2.2μF/25V	15VDC	1μF/25V

Recommended test circuit



EMC recommended circuit value table		
Emissions	C1	4.7μF /50V
Emissions	C2	4.7μF /50V
Emissions	CY	1nF/4kV
Emissions	C3	Recommended Test Circuit
Emissions	L	6.8μH

Mechanical dimensions



Unit:mm Unless otherwise specified, all tolerances are ±0.25

PIN	Single
1	-Vin
2	+Vin
4	-Vout
5	+Vout
8	NC
Other	NO PIN

1T8A2_3UP series

1W - Single Output DC-DC Converter - Fixed Input - Isolated & Unregulated

RoHS compliant type

Our RoHS parts just can withstand IR Reflow peak temperature: 240°C MAX as the following profile:

Profile Feature	Pb-Free Assembly
Average Ramp-Up Rate (Ts max to Tp)	3°C /second max.
<u>Preheat</u> -Temperature Min (Ts min) -Temperature Max (Ts max) -Time (ts min to ts max)	150°C 200°C 60-180 seconds
<u>Time maintained above</u> -Temperature (TL) -Time (tL)	217°C 60-150 seconds
Peak/Classification Temperature (Tp)	240°C max.
Time within 5°C of actual Peak Temperature (tp)	20-40 seconds
Ramp-Down Rate	6°C/seconds max.
Time 25°C to Peak Temperature	6 minutes max.

