


Datasheet

Manufacturer Part No.: T24CA117 ... T24CA0125

Cable Gland Sets, PG Thread

Part-No.: T24CA117 ... T24CA125



Black



Grey



White

Cable glands in PG design enable cables to be safely fed in and out of enclosures or machines. They protect the transition from the inside to the outside against dirt, dust and moisture and at the same time provide strain relief for the cable. This polyamide 6.6 version is highly resistant to external influences and can cover a wide operating temperature range.

Technical data: Material: Polyamide 6.6 // Seal: NBR • Temp-range -20 ... 80 °C • Thread type: PG • RoHS • REACH • IP68

Part-No.	Thread	Cable range (ø)	Thread length (TL)	Thread diameter (TD)	Length (GL)	Outside Diameter (GD)	Color	Content	EAN / GTIN
T24CA117	PG7 PG9 PG13.5 PG19 (10 pcs./each)	3.5 - 15 mm	6 - 9.5 mm	12 - 23 mm	27 - 34 mm	16 - 28.5 mm	Black	40 pcs.	4260732288831
T24CA118	PG7 PG9 PG11 PG13.5 (10 pcs./each)	3.5 - 12 mm	6 - 8 mm	12 - 18.5 mm	27 - 33 mm	16 - 23.5 mm	Black	40 pcs.	4260732288848
T24CA119	PG7 (20x) PG9 (10x) PG13.5 (10x)	3.5 - 12 mm	6 - 8 mm	12 - 18.5 mm	27 - 33 mm	16 - 23.5 mm	Black	40 pcs.	4260732288855
T24CA120	PG7 PG9 PG13.5 PG19 (10 pcs./each)	3.5 - 15 mm	6 - 9.5 mm	12 - 23 mm	27 - 34 mm	16 - 28.5 mm	Grey	40 pcs.	4260732288862
T24CA121	PG7 PG9 PG11 PG13.5 (10 pcs./each)	3.5 - 12 mm	6 - 8 mm	12 - 18.5 mm	27 - 33 mm	16 - 23.5 mm	Grey	40 pcs.	4260732288879
T24CA122	PG7 (20x) PG9 (10x) PG13.5 (10x)	3.5 - 12 mm	6 - 8 mm	12 - 18.5 mm	27 - 33 mm	16 - 23.5 mm	Grey	40 pcs.	4260732288886
T24CA123	PG7 PG9 PG13.5 PG19 (10 pcs./each)	3.5 - 15 mm	6 - 9.5 mm	12 - 23 mm	27 - 34 mm	16 - 28.5 mm	White	40 pcs.	4260732288893
T24CA124	PG7 PG9 PG11 PG13.5 (10 pcs./each)	3.5 - 12 mm	6 - 8 mm	12 - 18.5 mm	27 - 33 mm	16 - 23.5 mm	White	40 pcs.	4260732288909
T24CA125	PG7 (20x) PG9 (10x) PG13.5 (10x)	3.5 - 12 mm	6 - 8 mm	12 - 18.5 mm	27 - 33 mm	16 - 23.5 mm	White	40 pcs.	4260732288916

Values single parts:

Thread	Cable range (ø)	Thread length (TL)	Thread diameter (TD)	Length (GL)	Outside Diameter (GD)
PG7	3.5 - 6 mm	6 mm	12 mm	27 mm	16 mm
PG9	4 - 8 mm	6.5 mm	13.5 mm	29 mm	19 mm
PG11	5 - 10 mm	7 mm	16.9 mm	32 mm	21.5 mm
PG13.5	6 - 12 mm	8 mm	18.5 mm	33 mm	23.5 mm
PG19	12 - 15 mm	9.5 mm	23 mm	34 mm	28.5 mm