




Part Number : [1300280048](#)
Product Description : Micro-Change (M12)
Double-Ended Cordset, 5 Poles, Male
(Straight) to Female (Straight), 22 AWG,
DeviceNet Thin Stranded Cable, 15.0m (49.21')
Length
Series Number : 130028
Status : Active
Product Category : Circular Industrial
Cordsets
Engineering Number : DND22A-M150



Documents & Resources

Drawings
[1300280048_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130028
Description	Micro-Change (M12) Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 22 AWG, DeviceNet Thin Stranded Cable, 15.0m (49.21') Length
IP Rating	IP67
Product Name	DeviceNet, Micro-Change (M12)
Protocol	N/A
Type	Double Ended
UPC	78678849594

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	7.24mm (.285")
Cable Length	15.0m (49.21')
Color - Cable Jacket	Gray
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None

Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Zinc Die-Cast
Material - Plating Mating	Gold
Net Weight	355.600/g
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	Shielded-Twisted Pair
Wire Size (AWG)	22