



Part Number : [1200980007](#)
Product Description : Micro-Change (M12)
Double-Ended Cordset, 5 Poles, Female
(Straight) to Male (Straight), 24 AWG, 2.0m
(6.56') Length, PROFIBUS PUR Cable Preferred
Version in Europe
Series Number : 120098
Status : Active
Product Category : Circular Industrial
Cordsets
Engineering Number : BB5S30PP4M020



Documents & Resources

Drawings
[1200980007_sd.pdf](#)

Specifications
[TS-120065-003-001.pdf](#)
[TS-120065-004-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead... per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120098
Description	Micro-Change (M12) Double-Ended Cordset, 5 Poles, Female (Straight) to Male (Straight), 24 AWG, 2.0m (6.56') Length, PROFIBUS PUR Cable Preferred Version in Europe
IP Rating	IP67
Product Name	Micro-Change (M12)
Protocol	EtherNet
Type	Double Ended
UPC	78678850724

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC/DC

Physical

Cable Diameter	8.00mm (.315")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Violet
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	Reverse
LED Indicator	None
Material - Cable Jacket	PUR

Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	184.611/g
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	Twisted Pair
Wire Size (AWG)	24