


2170905	DATA SHEET	
Valid from: 29.05.2018	ETHERLINE® FIRE Cat.5e PH120 4x2x23/1AWG	

Description

ETHERLINE® FIRE Cat.5e PH120 is a CATEGORY 5e high speed data transmission cable with isolation integrity suitable for application in the industrial environments. The high quality screen ensures high transmission reliability of data transfer in electromagnetically polluted areas.



General characteristics

Conductor	Solid bare copper wire, AWG 23/1 or approx. 0.25 mm ²	
Insulation	solid polyethylene core Ø approx. 0.95 mm	
Core identification code	Pair 1: white/blue – blue Pair 3: white/green – green	Pair 2: white/orange – orange Pair 4: white/brown – brown
Core-wrapping	special tape (fire barrier)	
Stranding	2 cores stranded to pair	
Pair-wrapping	plastic-tape	
Overall stranding	4 pairs are separated by a central cross element	
Wrapping	special tape (fire barrier)	
Screening	plastic laminated metal foil with drain wire (26/1 AWG)	
Outer sheath	Flame retardant special compound color: red, similar to RAL 3000 outer Ø: approx. 8.6 mm	

Mechanical characteristics

Minimum bending radius	fixed installation: 15 x cable Ø
Permissible temperature range	fixed installation: -20 °C up to +70 °C
Flame propagation	flame retardant acc. to IEC 60332-1-2 insulation integrity class PH 120 acc. to EN50200
Halogen free	acc. to IEC 60754-1
Halogen acid gas contents	acc. to IEC 60754-2

Creator: TOST/PDC Released: ALTE/PDC	Document: DB2170905EN Version: 03	Page 1 of 2
---	--------------------------------------	-------------

2170905	DATA SHEET	
Valid from: 29.05.2018	ETHERLINE® FIRE Cat.5e PH120 4x2x23/1AWG	

Electrical characteristics

DC-Resistance (loop)	max. 134.0 Ω /km
Insulation resistance	min. 2 G Ω x km
Mutual capacitance	nom. 65 nF/km at 1 kHz
Characteristic impedance	nom. 100 Ω acc. to IEC 61156-5
Operating peak voltage	125 V (not for power purposes)
Velocity of propagation	approx. 0.67 c
Signal propagation time	nom. 510 ns/100m
Test voltage	core/core: 700 V core/screen: 700 V

Transmission properties

Transmission properties acc. to IEC 61156-5 for Category Cat.5e:

f [MHz]	Attenuation [dB/100m]	PS NEXT [dB]	EL FEXT [dB]	Return Loss [dB]
	Standard	Standard	Standard	Standard
1*	2.1	62.3	64.0	20.0
4	4.1	53.3	52.0	23.0
10	6.5	47.3	44.0	25.0
16	8.3	44.2	39.9	25.0
31,25	11.7	39.9	34.1	23.6
62,5	17.0	35.4	28.1	21.5
100	22.0	32.3	24.0	20.1

* Extract of normative minimum requirements

Standard

EU-Directive	Dangerous and forbidden substances acc. to RoHS directive (2011/65/EU) are not allowed to the manufacturing.
--------------	--

Creator: TOST/PDC Released: ALTE/PDC	Document: DB2170905EN Version: 03	Page 2 of 2
---	--------------------------------------	-------------

We reserve all rights according to DIN ISO 16016.

PD 0019/05_04.18EN