Part Number : 1200888083
Product Description : Nano-Change (M8) Single-Ended Cordset, 3 Poles, Female (Straight) with Snap Coupling to Pigtail, 24 AWG, PVC/PUR Cable, 1.0m (3.28') Length, PUR Cable Preferred Version in Europe
Series Number : 120088
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : 503000P02M020



Documents & Resources

Drawings
1200888083_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Triphenyl-phosphate per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120088
Description	Nano-Change (M8) Single-Ended Cordset, 3 Poles, Female (Straight) with Snap Coupling to Pigtail, 24 AWG, PVC/PUR Cable, 1.0m (3.28') Length, PUR Cable Preferred Version in Europe
IP Rating	IP67
Product Name	Nano-Change (M8)
Protocol	N/A
Type	Single Ended
UPC	78172532456

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC / 75V DC

Physical

Cable Diameter	N/A
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
Coupling Style	Snap
Gender	Female-Pigtail
Keyway	None
LED Indicator	None
Material - Cable Jacket	PUR/PVC
Material - Connector Body	TPE
Material - Contact	Copper Alloy

Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Orientation	Straight to Pigtail
Poles	3
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	N/A
Wire Size (AWG)	24

This document was generated on Feb 26, 2025