
Part Number : 1203410751
Product Description : Micro-Change (M12) to Standard RJ-45 CAT6A Double-Ended Cordset, 8 Poles, X-Coded, Female (Straight) to Male RJ-45 (Straight), 26 AWG, Green Shielded PUR Cable, 1.0m (3.28') Length
Series Number : 120341
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : ERWPEU7020M010



Documents & Resources

Drawings

1203410751_sd.pdf
PK-120341-170-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Reviewed per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead... per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120341
Description	Micro-Change (M12) to Standard RJ-45 CAT6A Double-Ended Cordset, 8 Poles, X-Coded, Female (Straight) to Male RJ-45 (Straight), 26 AWG, Green Shielded PUR Cable, 1.0m (3.28') Length
IP Rating	IP20, IP67 (M12 only)
Performance Category	6A
Product Name	Micro-Change (M12) Cat6A,RJ45,Industrial Ethernet
Protocol	EtherNet
Type	Double Ended
UPC	887191906621

Agency

UL	E200650

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	30V AC (RMS) / 42V DC

Physical

Cable Diameter	6.90mm (.272”)
Cable Length	1.0m (3.28')
Color - Cable Jacket	Green
Connector End A	Micro-Change (M12)
Connector End B	RJ-45 (standard)
Coupling Style	Threaded

Gender	Female-Male
Keyway	X-Coded
LED Indicator	None
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	94.300/g
Orientation	Straight to Straight
Poles	8
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	Shielded PUR
Wire Size (AWG)	26