



Part Number : [1300390157](#)
Product Description : Mini-Change to Micro-Change (M12) Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 22 AWG, Gray DeviceNet Standard Cable Plus Drain, 1.0m (3.28') Length
Series Number : 130039
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : DND21A-M010



Documents & Resources

Drawings
[1300390157_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130039
Description	Mini-Change to Micro-Change (M12) Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 22 AWG, Gray DeviceNet Standard Cable Plus Drain, 1.0m (3.28') Length
IP Rating	IP67
Product Name	DeviceNet, Micro-Change (M12), Mini-Change
Type	Double Ended
UPC	78678801117

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	6.86mm (.270")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Gray
Connector End A	Mini-Change
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single

LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Zinc Die-Cast
Material - O-Ring	Nitrile Rubber
Material - Plating Mating	Gold
Net Weight	65.650/g
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	Thin (Drop)
Wire Size (AWG)	22