



Part Number : [1200668234](#)
Product Description : Micro-Change (M12)
Double-Ended Cordset, 4 Poles, Male
(Straight) to Female (Straight), 0.34mm² Black
PUR LSOH Cable, 2.0m (6.56') Length
Series Number : 120066
Status : Active
Product Category : Circular Industrial
Cordsets
Engineering Number : 884030H09M020



Documents & Resources

Drawings
[1200668234_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead... per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120066
Description	Micro-Change (M12) Double-Ended Cordset, 4 Poles, Male (Straight) to Female (Straight), 0.34mm ² Black PUR LSOH Cable, 2.0m (6.56') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	883906600440

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

Physical

Cable Diameter	4.70mm (.185")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PUR

Material - Connector Body	TPU
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	90.900/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	UL 21198
Wire Size (AWG)	22