



Part Number : [2153452122](#)
Product Description : Pre-Crimped Lead
Squba 3.6 Female-to-Squba 3.6 Female, Tin
(Sn) Plating, 150.00mm Length, 16 AWG, Red
Series Number : 215345
Status : Active
Product Category : Power and Signal Cable
Assemblies



Documents & Resources

Drawings
[2153452122_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	215345
Description	Pre-Crimped Lead Squba 3.6 Female-to-Squba 3.6 Female, Tin (Sn) Plating, 150.00mm Length, 16 AWG, Red
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Squba Crimp Terminals
Product Name	Squba
UPC	195842349377

Electrical

Current - Maximum per Contact	14.0A
Voltage - Maximum	600V

Physical

Cable Length	150.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Red
Gender	Female-Female
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Resin	Modified Polystyrene
Net Weight	3.188/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	3.60mm
Plating min - Mating	2.540µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 11028

Wire Insulation Diameter	1.90mm-2.40mm
Wire Size (AWG)	16