



Part Number : [1200665404](#)
Product Description : Micro-Change (M12) Double-Ended Cordset, 12 Poles, Female (Straight) to Male (Straight), 26 AWG, PUR Cable, 1.0m (3.28') Length
Series Number : 120066
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : 88C030H45M010



Documents & Resources

Drawings
[1200665404_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120066
Description	Micro-Change (M12) Double-Ended Cordset, 12 Poles, Female (Straight) to Male (Straight), 26 AWG, PUR Cable, 1.0m (3.28') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	884982224445

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	30V AC/DC

Physical

Cable Diameter	6.00mm (.236")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PUR
Material - Connector Body	PUR

Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	87.411/g
Orientation	Straight to Straight
Poles	12
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	UL 20549
Wire Size (AWG)	26

This document was generated on Feb 26, 2025