








SECTION E-E





SECTION F-F




- NOTES:
1. MATERIALS:
HOUSINGS: SPS/NYLON BLEND, GLASS FILLED, UL 94 HB
SEAL: SILICONE RUBBER
 2. EXTERNAL SURFACES CLASS C PER MOLEX STANDARD PS-45499-002. VARIATION OF SHADE WITHIN OR BETWEEN BATCHES, OR DISCOLOURATION IS ACCEPTABLE.
 3. MX150 BLADE TERMINALS PER SD-33000-001 TO BE USED WITH THESE ASSEMBLIES IN CAVITIES B, C, D, E AND F, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 1.5mm TO 2.7mm
 4. MX150L BLADE TERMINALS PER SD-19431-00* TO BE USED WITH THESE ASSEMBLIES IN CAVITIES A AND G, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 3.0mm TO 5.0mm
 5. PRODUCT SPECIFICATION: 850830010 PSP
 6. PACKAGING SPECIFICATION: 937921000 PSK
 7. MATES WITH: SRC 60+6AG POWER RECEPTACLE HOUSING (BLACK)
PART NUMBER 850840700 PER 850840700 PSD
 8. APPLICATION SPECIFICATION: 850830010 PSA
 9. FLANGE GASKET OPTION: REFER TO 850710017 PSD

ACCEPTABLE CABLE INSULATION Ø RANGES (mm) - NOTES 3 & 4						
CAVITY SET						
G	F	E	D	C	B	A
3.0 - 5.0	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	3.0 - 5.0

4	MALE BACK SEAL	1	RUST RED
3	MALE REAR COVER	1	BLACK
2	MALE FRONT COVER	1	GREEN
1	MALE HOUSING	1	BLACK
No.	DESCRIPTION	QTY	COLOUR
BILL OF MATERIAL			




SECTION G-G



QUALITY SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
▽A = 0	ADD GREEN OPTIONS	EC NO: 114187	2017/04/12	DRWN: SMCGREEVY	2017/06/30	CHKD: AJOBRIEN	2017/07/03	APPR: JDWALLACE	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION UNITS	SCALE
▽E = 0									MM	1:1	
▽F = 0									ANGULAR TOL ± °	DRWN BY	DATE
▽ = 0									4 PLACES ±	AJOBRIEN	2015/08/07
▽ = 0									3 PLACES ±	CHK'D BY	DATE
▽ = 0									2 PLACES ± 0.2	SMCGREEVY	2015/08/14
▽ = 0									1 PLACE ± 0.5	APPR BY	DATE
▽ = 0									0 PLACES ±	JDWALLACE	2015/09/03
▽ = 0									DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DRAWING SIZE	THIRD ANGLE PROJECTION
▽ = 0									A2		
										molex	
										SRC MIXED POWER MALE BLADE HOUSING ASSEMBLY	
										PRODUCT CUSTOMER DRAWING	
										SERIES	MATERIAL NUMBER
										93792	937926006
										CUSTOMER	GENERAL MARKET
										DOCUMENT NUMBER	SHEET NUMBER
										937921000	1 OF 16
										DOC TYPE	DOC PART
										PSD	000



72+2D MAIN HOUSING BLACK




SECTION H-H

ACCEPTABLE CABLE INSULATION Ø RANGES (mm) - NOTES 2 & 3						
CAVITY SET						
G	F	E	D	C	B	A
1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	3.0 - 5.0	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7


4	MALE BACK SEAL	1	RUST RED
3	MALE REAR COVER	1	BLACK
2	MALE FRONT COVER	1	GREEN
1	MALE HOUSING	1	BLACK
No.	DESCRIPTION	QTY	COLOUR
BILL OF MATERIAL			



- NOTES:
1. REFERENCE SHEET 1 FOR UNSPECIFIED NOTES AND DIMENSIONS
 2. MX150 BLADE TERMINALS PER SD-33000-001 TO BE USED WITH THIS ASSEMBLY IN CAVITIES A, B, C, E, F AND G, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 1.5mm TO 2.7mm
 3. MX150L BLADE TERMINALS PER SD-19431-00* TO BE USED WITH THIS ASSEMBLY IN CAVITY D CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 3.0mm TO 5.0mm
 4. MATES WITH: SRC 72+2D POWER RECEPTACLE HOUSING ASSEMBLY (BLACK) PART NUMBER 850847202 PER 850840700 PSD

QUALITY SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																								
FA = 0 FB = 0 FD = 0 ▼ = 0 C = 0 ⊠ = 0 ■ = 0 ▽ = 0 <td rowspan="10">ADD GREEN OPTIONS</td><td rowspan="10">2017/04/12 2017/06/30 2017/07/03</td><td rowspan="10">2017/06/30 2017/07/03</td><td rowspan="10">2017/07/03</td><td rowspan="10">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td rowspan="10">ANGULAR TOL ± °</td><td rowspan="10">4 PLACES ±</td><td rowspan="10">3 PLACES ±</td><td rowspan="10">2 PLACES ± 0.2</td><td rowspan="10">1 PLACE ± 0.5</td><td rowspan="10">0 PLACES ±</td><td rowspan="10">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td rowspan="10">DIMENSION UNITS MM</td><td rowspan="10">SCALE 1:1</td><td colspan="6" rowspan="2">molex®</td>	ADD GREEN OPTIONS	2017/04/12 2017/06/30 2017/07/03	2017/06/30 2017/07/03	2017/07/03	GENERAL TOLERANCES (UNLESS SPECIFIED)	ANGULAR TOL ± °	4 PLACES ±	3 PLACES ±	2 PLACES ± 0.2	1 PLACE ± 0.5	0 PLACES ±	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION UNITS MM	SCALE 1:1	molex®										
AJOBRIEN 2015/08/07															SRC MIXED POWER MALE BLADE HOUSING ASSEMBLY										
CHK'D BY DATE SMCGREEVY 2015/08/14																									
APPR BY DATE JDWALLACE 2015/09/03															PRODUCT CUSTOMER DRAWING										
DRAWING SIZE A3																					THIRD ANGLE PROJECTION 				
SERIES 93792															MATERIAL NUMBER 937927202				CUSTOMER GENERAL MARKET						
DOCUMENT NUMBER 937921000															DOC TYPE PSD		DOC PART 000		SHEET NUMBER 2 OF 16						


48+8ADG MAIN HOUSING BLACK



SECTION J-J

ACCEPTABLE CABLE INSULATION Ø RANGES (mm) - NOTES 2 & 3						
CAVITY SET						
G	F	E	D	C	B	A
3.0 - 5.0	1.5 - 2.7	1.5 - 2.7	3.0 - 5.0	1.5 - 2.7	1.5 - 2.7	3.0 - 5.0

4	MALE BACK SEAL	1	RUST RED
3	MALE REAR COVER	1	BLACK
2	MALE FRONT COVER	1	GREEN
1	MALE HOUSING	1	BLACK
No.	DESCRIPTION	QTY	COLOUR
BILL OF MATERIAL			



TERMINAL
POSITION G3


17.8 REF.

TERMINAL
POSITION A3

TERMINAL
POSITION G1


11.0 REF.

TERMINAL
POSITION A1




NOTES:

1. REFERENCE SHEET 1 FOR UNSPECIFIED NOTES AND DIMENSIONS
2. MX150 BLADE TERMINALS PER SD-33000-001 TO BE USED WITH THIS ASSEMBLY IN CAVITIES B, C, E AND F, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 1.5mm TO 2.7mm
3. MX150L BLADE TERMINALS PER SD-19431-00* TO BE USED WITH THIS ASSEMBLY IN CAVITIES A, D AND G, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 3.0mm TO 5.0mm
4. MATES WITH: SRC 48+8ADG POWER RECEPTACLE HOUSING ASSEMBLY (BLACK)
PART NUMBER 850844808 PER 850840700 PSD

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		
QUALITY SYMBOLS		ADD GREEN OPTIONS EC NO: 114187 DRWN: SMCGREEVY CHK'D: AJOBRIEN APPR: JDWALLACE			GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®							
							MM		1:1									
FA = 0					ANGULAR TOL ± °		DRWN BY		DATE		SRC MIXED POWER MALE BLADE HOUSING ASSEMBLY							
FE = 0							AJOBRIEN		2015/08/07									
FD = 0					CHK'D BY		DATE											
▼ = 0					SMCGREEVY		2015/08/14											
C = 0					4 PLACES		±		APPR BY		DATE		PRODUCT CUSTOMER DRAWING					
⊠ = 0					3 PLACES		±		JDWALLACE		2015/09/03							
■ = 0					2 PLACES		± 0.2		DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES		MATERIAL NUMBER		CUSTOMER	
▽ = 0					1 PLACE		± 0.5						93792		937924808		GENERAL MARKET	
		0 PLACES		±		A3				DOCUMENT NUMBER				DOC TYPE	DOC PART	SHEET NUMBER		
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								937921000				PSD	000	3 OF 16		



36+12ACEG MAIN HOUSING BLACK




SECTION K-K

ACCEPTABLE CABLE INSULATION Ø RANGES (mm) - NOTES 2 & 3						
CAVITY SET						
G	F	E	D	C	B	A
3.0 - 5.0	1.5 - 2.7	3.0 - 5.0	1.5 - 2.7	3.0 - 5.0	1.5 - 2.7	3.0 - 5.0


4	MALE BACK SEAL	1	RUST RED
3	MALE REAR COVER	1	BLACK
2	MALE FRONT COVER	1	GREEN
1	MALE HOUSING	1	BLACK
No.	DESCRIPTION	QTY	COLOUR
BILL OF MATERIAL			



- NOTES:
- REFERENCE SHEET 1 FOR UNSPECIFIED NOTES AND DIMENSIONS
 - MX150 BLADE TERMINALS PER SD-33000-001 TO BE USED WITH THIS ASSEMBLY IN CAVITIES B, D AND F, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 1.5mm TO 2.7mm
 - MX150L BLADE TERMINALS PER SD-19431-00* TO BE USED WITH THIS ASSEMBLY IN CAVITIES A, C, E AND G, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 3.0mm TO 5.0mm
 - MATES WITH: SRC 36+12ACEG POWER RECEPTACLE HOUSING ASSEMBLY (BLACK)
PART NUMBER 850843612 PER 850840700 PSD

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
QUALITY SYMBOLS		ADD GREEN OPTIONS EC NO: 114187 DRWN: SMCGREEVY CHK'D: AJOBRIEN APPR: JDWALLACE 2017/04/12 2017/06/30 2017/07/03				GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®		
 = 0						ANGULAR TOL ± °		MM		1:1				
 = 0						4 PLACES ±		DRWN BY		DATE		SRC MIXED POWER MALE BLADE HOUSING ASSEMBLY		
 = 0						3 PLACES ±		AJOBRIEN		2015/08/07				
 = 0						2 PLACES ± 0.2		CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING		
 = 0						1 PLACE ± 0.5		SMCGREEVY		2015/08/14				
 = 0						0 PLACES ±		APPR BY		DATE		SERIES		
 = 0						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		JDWALLACE		2015/09/03				
 = 0	B4	REV		DRAWING SIZE		THIRD ANGLE PROJECTION		MATERIAL NUMBER		CUSTOMER				
				A3				937923612		GENERAL MARKET				
								DOCUMENT NUMBER		DOC TYPE	DOC PART	SHEET NUMBER		
								937921000		PSD	000	4 OF 16		



24+14ACDEG MAIN HOUSING BLACK




SECTION L-L

ACCEPTABLE CABLE INSULATION Ø RANGES (mm) - NOTES 2 & 3						
CAVITY SET						
G	F	E	D	C	B	A
3.0 - 5.0	1.5 - 2.7	3.0 - 5.0	3.0 - 5.0	3.0 - 5.0	1.5 - 2.7	3.0 - 5.0


4	MALE BACK SEAL	1	RUST RED
3	MALE REAR COVER	1	BLACK
2	MALE FRONT COVER	1	GREEN
1	MALE HOUSING	1	BLACK
No.	DESCRIPTION	QTY	COLOUR
BILL OF MATERIAL			



- NOTES:
1. REFERENCE SHEET 1 FOR UNSPECIFIED NOTES AND DIMENSIONS
 2. MX150 BLADE TERMINALS PER SD-33000-001 TO BE USED WITH THIS ASSEMBLY IN CAVITIES B AND F, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 1.5mm TO 2.7mm
 3. MX150L BLADE TERMINALS PER SD-19431-00* TO BE USED WITH THIS ASSEMBLY IN CAVITIES A, C, D, E AND G, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 3.0mm TO 5.0mm
 4. MATES WITH: SRC 24+14ACDEG POWER RECEPTACLE HOUSING ASSEMBLY (BLACK)
PART NUMBER 850842414 PER 850840700 PSD

QUALITY SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
FA = 0 FE = 0 FED = 0 ▽ = 0 C = 0 ⊠ = 0 ■ = 0 ▽ = 0	ADD GREEN OPTIONS EC NO: 114187 DRWN: SMCGREEVY CHK'D: AJOBRIEN APPR: JDWALLACE		2017/04/12 2017/06/30 2017/07/03		GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± ° 4 PLACES ± 3 PLACES ± 2 PLACES ± 0.2 1 PLACE ± 0.5 0 PLACES ± DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DIMENSION UNITS		SCALE		molex® SRC MIXED POWER MALE BLADE HOUSING ASSEMBLY PRODUCT CUSTOMER DRAWING						
MM							1:1										
DRWN BY							DATE										
AJOBRIEN							2015/08/07										
CHK'D BY							DATE										
SMCGREEVY							2015/08/14										
APPR BY							DATE										
JDWALLACE							2015/09/03										
DRAWING SIZE							THIRD ANGLE PROJECTION		SERIES		MATERIAL NUMBER			CUSTOMER			
A3									93792		937922414			GENERAL MARKET			
				DOCUMENT NUMBER			DOC TYPE		DOC PART		SHEET NUMBER						
				937921000			PSD		000		5 OF 16						


12+18ABCEFG MAIN HOUSING BLACK



SECTION M-M

ACCEPTABLE CABLE INSULATION Ø RANGES (mm) - NOTES 2 & 3						
CAVITY SET						
G	F	E	D	C	B	A
3.0 - 5.0	3.0 - 5.0	3.0 - 5.0	1.5 - 2.7	3.0 - 5.0	3.0 - 5.0	3.0 - 5.0

4	MALE BACK SEAL	1	RUST RED
3	MALE REAR COVER	1	BLACK
2	MALE FRONT COVER	1	GREEN
1	MALE HOUSING	1	BLACK
No.	DESCRIPTION	QTY	COLOUR
BILL OF MATERIAL			



TERMINAL
POSITION G3


15.0 REF

TERMINAL
POSITION A3

TERMINAL
POSITION G1

13.0 REF

TERMINAL
POSITION A1




NOTES:

1. REFERENCE SHEET 1 FOR UNSPECIFIED NOTES AND DIMENSIONS
2. MX150 BLADE TERMINALS PER SD-33000-001 TO BE USED WITH THIS ASSEMBLY IN CAVITY D CRIMPED, WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 1.5mm TO 2.7mm
3. MX150L BLADE TERMINALS PER SD-19431-00* TO BE USED WITH THIS ASSEMBLY IN CAVITY A, B, C, E, F AND G, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 3.0mm TO 5.0mm
4. MATES WITH: SRC 12+18ABCEFG POWER RECEPTACLE HOUSING ASSEMBLY (BLACK)
PART NUMBER 850841218 PER 850840700 PSD

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			
QUALITY SYMBOLS		ADD GREEN OPTIONS		EC NO: 114187 DRWN: SMCGREEVY CHK'D: AJOBRIEN APPR: JDWALLACE		2017/04/12 2017/06/30 2017/07/03		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®					
										MM		1:1							
F A = 0										ANGULAR TOL ± °		DRWN BY		DATE		SRC MIXED POWER MALE BLADE HOUSING ASSEMBLY			
F E = 0												AJOBRIEN		2015/08/07					
F D = 0												CHK'D BY		DATE					
▽ = 0												SMCGREEVY		2015/08/14					
C = 0												APPR BY		DATE					
⊠ = 0												JDWALLACE		2015/09/03					
■ = 0												DRAWING SIZE		THIRD ANGLE PROJECTION					
∇ = 0												A3							
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																	
		B4		REV								SERIES		MATERIAL NUMBER		CUSTOMER			
												93792		937921218		GENERAL MARKET			
												DOCUMENT NUMBER		DOC TYPE		DOC PART		SHEET NUMBER	
												937921000		PSD		000		6 OF 16	


0+20ABCDEFGG MAIN HOUSING BLACK



SECTION N-N

ACCEPTABLE CABLE INSULATION Ø RANGES (mm) - NOTE 2						
CAVITY SET						
G	F	E	D	C	B	A
3.0 - 5.0	3.0 - 5.0	3.0 - 5.0	3.0 - 5.0	3.0 - 5.0	3.0 - 5.0	3.0 - 5.0

4	MALE BACK SEAL	1	RUST RED
3	MALE REAR COVER	1	BLACK
2	MALE FRONT COVER	1	GREEN
1	MALE HOUSING	1	BLACK
No.	DESCRIPTION	QTY	COLOUR
BILL OF MATERIAL			



TERMINAL
POSITION G3


TERMINAL
POSITION G1

11.00 REF

TERMINAL
POSITION A3

17.80 REF

TERMINAL
POSITION A1




NOTES:

1. REFERENCE SHEET 1 FOR UNSPECIFIED NOTES AND DIMENSIONS
2. MX150L BLADE TERMINALS PER SD-19431-00* TO BE USED WITH THIS ASSEMBLY IN ALL CAVITIES CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 3.0mm TO 5.0mm
3. MATES WITH: SRC 0+20ABCDEFGG POWER RECEPTACLE HOUSING ASSEMBLY (BLACK)
PART NUMBER 850840020 PER 850840700 PSD

QUALITY SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		
	= 0	ADD GREEN OPTIONS	EC NO: 114187 DRWN: SMCGREEVY CHK'D: AJOBRIEN APPR: JDWALLACE	2017/04/12 2017/06/30 2017/07/03	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE											
	= 0						MM		1:1											
	= 0						DRWN BY								DATE					
	= 0						AJOBRIEN								2015/08/07					
	= 0						CHK'D BY								DATE					
	= 0						SMCGREEVY								2015/08/14					
	= 0						APPR BY				DATE				PRODUCT CUSTOMER DRAWING					
	= 0						JDWALLACE				2015/09/03									
	= 0						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE		THIRD ANGLE PROJECTION				SERIES		MATERIAL NUMBER		CUSTOMER	
	= 0								A3						93792		937920020		GENERAL MARKET	
	= 0	REV		B4						DOCUMENT NUMBER		DOC TYPE		DOC PART		SHEET NUMBER				
	= 0									937921000		PSD		000		7 OF 16				



84+0 (2.5) MAIN HOUSING BLACK




ACCEPTABLE CABLE INSULATION Ø RANGES (mm) - NOTES 2 & 3
(COMBINATIONS OF CABLES PER NOTES 2 & 3 ALLOWED IN B & F)

CAVITY SET						
G	F	E	D	C	B	A
1.5 - 2.7	1.5 - 3.0	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 3.0	1.5 - 2.7


4	MALE BACK SEAL	1	RUST RED
3	MALE REAR COVER	1	BLACK
2	MALE FRONT COVER	1	GREEN
1	MALE HOUSING	1	BLACK
No.	DESCRIPTION	QTY	COLOUR
BILL OF MATERIAL			



- NOTES:
- REFERENCE SHEET ONE FOR UNSPECIFIED NOTES AND DIMENSIONS
 - MX150 BLADE TERMINAL PER SD-33000-001 TO BE USED WITH THIS ASSEMBLY IN ALL CAVITIES, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 1.5mm TO 2.7mm
 - SRC BLADE TERMINALS PER 936420010 PSD MAY BE USED WITH THIS ASSEMBLY IN CAVITIES B AND F CRIMPED WITH 2.5mm² (13AWG) CABLE INSULATION OUTER DIAMETER IN THE RANGE 2.7mm TO 3.0mm
 - MATES WITH: SRC2 84 PIN 2.5 RECEPTACLE HOUSING ASSEMBLY (BLACK) PART NUMBER 932878425 PER 932870001 PSD

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		
QUALITY SYMBOLS		ADD GREEN OPTIONS EC NO: 114187 DRWN: SMCGREEVY CHK'D: AJOBRIEN APPR: JDWALLACE 2017/04/12 2017/06/30 2017/07/03				GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®						
 = 0						ANGULAR TOL ± °		MM		1:1								
 = 0						4 PLACES ±		DRWN BY		DATE		SRC MIXED POWER MALE BLADE HOUSING ASSEMBLY						
 = 0						3 PLACES ±		AJOBRIEN		2015/08/07								
 = 0						2 PLACES ± 0.2		CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING						
 = 0						1 PLACE ± 0.5		SMCGREEVY		2015/08/14								
 = 0						0 PLACES ±		APPR BY		DATE		SERIES 93792					MATERIAL NUMBER 937928425	
 = 0		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		JDWALLACE		2015/09/03		DOCUMENT NUMBER 937921000										
 = 0		B4		REV		A3												
 = 0																		

60+6AG (2.5) MAIN HOUSING BLACK





SECTION R-R

ACCEPTABLE CABLE INSULATION Ø RANGES (mm) - NOTES 2, 3 & 4
(COMBINATIONS OF CABLES PER NOTES 2 & 3 ALLOWED IN B & F)

CAVITY SET						
G	F	E	D	C	B	A
3.0 - 5.0	1.5 - 3.0	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 3.0	3.0 - 5.0


4	MALE BACK SEAL	1	RUST RED
3	MALE REAR COVER	1	BLACK
2	MALE FRONT COVER	1	GREEN
1	MALE HOUSING	1	BLACK
No.	DESCRIPTION	QTY	COLOUR
BILL OF MATERIAL			



- NOTES:
- REFERENCE SHEET 1 FOR UNSPECIFIED NOTES AND DIMENSIONS
 - MX150 BLADE TERMINALS PER SD-33000-001 TO BE USED WITH THIS ASSEMBLY IN CAVITIES B, C, D, E AND F, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 1.5mm TO 2.7mm
 - SRC BLADE TERMINALS PER 936420010 PSD MAY BE USED WITH THIS ASSEMBLY IN CAVITIES B AND F, CRIMPED WITH 2.5mm² (13AWG) CABLE INSULATION OUTER DIAMETER IN THE RANGE 2.7mm TO 3.0mm
 - MX150L BLADE TERMINALS PER SD-19431-00* TO BE USED WITH THIS ASSEMBLY IN CAVITIES A AND G, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 3.0mm TO 5.0mm
 - MATES WITH: SRC 60+6AG POWER 2.5 RECEPTACLE HOUSING ASSEMBLY (BLACK)
PART NUMBER 850846025 PER 850840700 PSD

QUALITY SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
▽A = 0 ▽F = 0 ▽E = 0 ▼ = 0 ▽C = 0 ⊠ = 0 ■ = 0 ▽ = 0	ADD GREEN OPTIONS	2017/04/12 2017/06/30 2017/07/03	EC NO: 114187 DRWN: SMCGREEVY CHK'D: AJOBRIEN APPR: JDWALLACE	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®						
						MM		1:1								
						ANGULAR TOL ±		DRWN BY		DATE		SRC MIXED POWER MALE BLADE HOUSING ASSEMBLY				
						4 PLACES ±		AJOBRIEN		2015/08/07						
						3 PLACES ±		CHK'D BY		DATE						
						2 PLACES ± 0.2		SMCGREEVY		2015/08/14						
						1 PLACE ± 0.5		APPR BY		DATE						
						0 PLACES ±		JDWALLACE		2015/09/03		PRODUCT CUSTOMER DRAWING				
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE		THIRD ANGLE PROJECTION						SERIES
						A3				93792		937926025		GENERAL MARKET		
DOCUMENT NUMBER		DOC TYPE		DOC PART						SHEET NUMBER						
937921000		PSD		000						9 OF 16						

84+0 MAIN HOUSING BLACK




SECTION T-T

ACCEPTABLE CABLE INSULATION Ø RANGES (mm) - NOTE 2

CAVITY SET

G	F	E	D	C	B	A
1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7

4	MALE BACK SEAL	1	RUST RED
3	MALE REAR COVER	1	BLACK
2	MALE FRONT COVER	1	GREEN
1	MALE HOUSING	1	BLACK
No.	DESCRIPTION	QTY	COLOUR
BILL OF MATERIAL			



TERMINAL
POSITION G12


TERMINAL
POSITION G7

11.0 REF

TERMINAL
POSITION A6

TERMINAL
POSITION A1

11.0 REF




NOTES:

1. REFERENCE SHEET 1 FOR UNSPECIFIED NOTES AND DIMENSIONS
2. MX150 BLADE TERMINALS PER SD-33000-001 TO BE USED WITH THIS ASSEMBLY IN ALL CAVITIES CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 1.5mm TO 2.7mm
3. MATES WITH SRC2 84 PIN RECEPTACLE HOUSING ASSEMBLY (BLACK) PART NUMBER 932870001 PER 932870001 PSD

QUALITY SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
= 0	ADD GREEN OPTIONS	EC NO: 114187 DRWN: SMCGREEVY CHK'D: AJOBRIEN APPR: JDWALLACE	2017/04/12 2017/06/30 2017/07/03	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex® SRC MIXED POWER MALE BLADE HOUSING ASSEMBLY PRODUCT CUSTOMER DRAWING			
= 0						MM		1:1					
= 0						DRWN BY							
= 0				AJOBRIEN				2015/08/07					
= 0				CHK'D BY				DATE					
= 0				SMCGREEVY				2015/08/14					
= 0				APPR BY				DATE					
= 0				JDWALLACE				2015/09/03					
= 0				DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES		MATERIAL NUMBER		CUSTOMER	
= 0				A3				93792		937928400		GENERAL MARKET	
= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				DOCUMENT NUMBER		DOC TYPE		DOC PART		SHEET NUMBER		
= 0	B4		REV		937921000		PSD		000		10 OF 16		



84+0 MAIN HOUSING GREEN



SECTION Y-Y

ACCEPTABLE CABLE INSULATION Ø RANGES (mm) - NOTE 2						
CAVITY SET						
G	F	E	D	C	B	A
1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7


4	MALE BACK SEAL	1	RUST RED
3	MALE REAR COVER	1	BLACK
2	MALE FRONT COVER	1	GREEN
1	MALE HOUSING	1	GREEN
No.	DESCRIPTION	QTY	COLOUR
BILL OF MATERIAL			



- NOTES:
- REFERENCE SHEET 1 FOR UNSPECIFIED NOTES AND DIMENSIONS
 - MX150 BLADE TERMINALS PER SD-33000-001 TO BE USED WITH THIS ASSEMBLY IN ALL CAVITIES CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 1.5mm TO 2.7mm
 - MATES WITH SRC2 84 PIN RECEPTACLE HOUSING ASSEMBLY (GREEN) PART NUMBER 938498400 PER 932870001 PSD

QUALITY SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
FA = 0 FE = 0 FED = 0 ▽ = 0 C = 0 ⊠ = 0 ■ = 0 ▽ = 0	ADD GREEN OPTIONS		2017/04/12 2017/06/30 2017/07/03		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex® SRC MIXED POWER MALE BLADE HOUSING ASSEMBLY		
EC NO: 114187 DRWN: SMCGREEVY CHK'D: AJOBRIEN APPR: JDWALLACE		2017/04/12 2017/06/30 2017/07/03		ANGULAR TOL ± °		MM		1:1					
				4 PLACES ±		AJOBRIEN		2015/08/07		PRODUCT CUSTOMER DRAWING			
				3 PLACES ±		CHK'D BY		DATE					
				2 PLACES ± 0.2		SMCGREEVY		2015/08/14					
				1 PLACE ± 0.5		APPR BY		DATE					
				0 PLACES ±		JDWALLACE		2015/09/03		SERIES 93792			
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE		THIRD ANGLE PROJECTION					MATERIAL NUMBER 938508400
						A3				CUSTOMER GENERAL MARKET			
										DOCUMENT NUMBER 937921000			
										DOC TYPE PSD			
										DOC PART 000			
										SHEET NUMBER 11 OF 16			

84+0 (2.5) MAIN HOUSING GREEN




SECTION Z-Z

ACCEPTABLE CABLE INSULATION Ø RANGES (mm) - NOTES 2 & 3
(COMBINATIONS OF CABLES PER NOTES 2 & 3 ALLOWED IN B & F)

CAVITY SET						
G	F	E	D	C	B	A
1.5 - 2.7	1.5 - 3.0	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 3.0	1.5 - 2.7

4	MALE BACK SEAL	1	RUST RED
3	MALE REAR COVER	1	BLACK
2	MALE FRONT COVER	1	GREEN
1	MALE HOUSING	1	GREEN
No.	DESCRIPTION	QTY	COLOUR
BILL OF MATERIAL			



TERMINAL
POSITION G12


15.0 REF.

TERMINAL
POSITION A6

TERMINAL
POSITION G7

17.8 REF.

TERMINAL
POSITION A1



NOTES:

1. REFERENCE SHEET ONE FOR UNSPECIFIED NOTES AND DIMENSIONS
2. MX150 BLADE TERMINAL PER SD-33000-001 TO BE USED WITH THIS ASSEMBLY IN ALL CAVITIES, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 1.5mm TO 2.7mm
3. SRC BLADE TERMINALS PER 936420010 PSD MAY BE USED WITH THIS ASSEMBLY IN CAVITIES B AND F CRIMPED WITH 2.5mm² (13AWG) CABLE INSULATION OUTER DIAMETER IN THE RANGE 2.7mm TO 3.0mm
4. MATES WITH: SRC2 84 PIN 2.5 RECEPTACLE HOUSING ASSEMBLY (GREEN) PART NUMBER 938498425 PER 932870001 PSD


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		
QUALITY SYMBOLS		ADD GREEN OPTIONS EC NO: 114187 DRWN: SMCGREEVY CHK'D: AJOBRIEN APPR: JDWALLACE 2017/04/12 2017/06/30 2017/07/03				GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex® SRC MIXED POWER MALE BLADE HOUSING ASSEMBLY						
								MM		1:1								
F = 0						ANGULAR TOL ± °				DRWN BY		DATE		PRODUCT CUSTOMER DRAWING				
E = 0						4 PLACES ±		AJOBRIEN		2015/08/07								
D = 0						3 PLACES ±		CHK'D BY		DATE		93792 938508425 GENERAL MARKET						
▽ = 0						2 PLACES ± 0.2		SMCGREEVY		2015/08/14								
C = 0						1 PLACE ± 0.5		APPR BY		DATE		DOCUMENT NUMBER 937921000 DOC TYPE PSD DOC PART 000 SHEET NUMBER 12 OF 16						
☒ = 0		0 PLACES ±		JDWALLACE		2015/09/03												
■ = 0		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				DRAWING SIZE		THIRD ANGLE PROJECTION										
▽ = 0		B4				A3												

Technical drawing of a mechanical assembly in cross-section. The drawing shows a base plate (1) supporting a central assembly (2) which includes a spring mechanism (4). The top plate (3) features a series of vertical pins or studs. Arrows indicate the following components:

- 1: Base plate
- 2: Central assembly
- 3: Top plate
- 4: Spring mechanism


ACCEPTABLE CABLE INSULATION Ø RANGES (mm) - NOTES 2 & 3						
CAVITY SET						
G	F	E	D	C	B	A
3.0 - 5.0	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	3.0 - 5.0

This diagram shows an exploded view of a 16-pin D-sub connector assembly. The components are color-coded: the housing is blue, the contact pins are red, and the contact sockets are green. The assembly includes a D-shaped shield, a housing with mounting tabs, a contact plate with 16 pins, and a contact plate with 16 sockets. The diagram illustrates how these parts fit together to form a secure connection.



FORMAT: master-tb-prod-A3 REVISION: G DATE: 2017/02/06	9	8
--	---	---



60+6AG (2.5) MAIN HOUSING GREEN



SECTION W-W

ACCEPTABLE CABLE INSULATION Ø RANGES (mm) - NOTES 2, 3 & 4 (COMBINATIONS OF CABLES PER NOTES 2 & 3 ALLOWED IN B & F)						
CAVITY SET						
G	F	E	D	C	B	A
3.0 - 5.0	1.5 - 3.0	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 3.0	3.0 - 5.0


4	MALE BACK SEAL	1	RUST RED
3	MALE REAR COVER	1	BLACK
2	MALE FRONT COVER	1	GREEN
1	MALE HOUSING	1	GREEN
No.	DESCRIPTION	QTY	COLOUR
BILL OF MATERIAL			



- NOTES:
- REFERENCE SHEET 1 FOR UNSPECIFIED NOTES AND DIMENSIONS
 - MX150 BLADE TERMINALS PER SD-33000-001 TO BE USED WITH THIS ASSEMBLY IN CAVITIES B, C, D, E AND F, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 1.5mm TO 2.7mm
 - SRC BLADE TERMINALS PER 936420010 PSD MAY BE USED WITH THIS ASSEMBLY IN CAVITIES B AND F, CRIMPED WITH 2.5mm² (13AWG) CABLE INSULATION OUTER DIAMETER IN THE RANGE 2.7mm TO 3.0mm
 - MX150L BLADE TERMINALS PER SD-19431-00* TO BE USED WITH THIS ASSEMBLY IN CAVITIES A AND G, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 3.0mm TO 5.0mm
 - MATES WITH: SRC 60+6AG POWER 2.5 RECEPTACLE HOUSING ASSEMBLY (GREEN)
- PART NUMBER 938496025 PER 850840700 PSD

QUALITY SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
▽^A = 0 ▽^F = 0 ▽^E = 0 ▼ = 0 ▽^C = 0 ⊠ = 0 ■ = 0 ▽^D = 0	ADD GREEN OPTIONS	2017/04/12 2017/06/30 2017/07/03	EC NO: 114187 DRWN: SMCGREEVY CHK'D: AJOBRIEN APPR: JDWALLACE	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®							
						MM		1:1									
						ANGULAR TOL ± °		DRWN BY		DATE		SRC MIXED POWER MALE BLADE HOUSING ASSEMBLY					
						4 PLACES ±		AJOBRIEN		2015/08/07							
						3 PLACES ±		CHK'D BY		DATE							
						2 PLACES ± 0.2		SMCGREEVY		2015/08/14							
						1 PLACE ± 0.5		APPR BY		DATE							
						0 PLACES ±		JDWALLACE		2015/09/03		PRODUCT CUSTOMER DRAWING					
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES	MATERIAL NUMBER		CUSTOMER		
						A3				93792	938506025		GENERAL MARKET				
DOCUMENT NUMBER		DOC TYPE	DOC PART	SHEET NUMBER													
937921000		PSD	000	14 OF 16													

48+8ADG MAIN HOUSING GREEN





SECTION U-U

ACCEPTABLE CABLE INSULATION Ø RANGES (mm) - NOTES 2 & 3

CAVITY SET

G	F	E	D	C	B	A
3.0 - 5.0	1.5 - 2.7	1.5 - 2.7	3.0 - 5.0	1.5 - 2.7	1.5 - 2.7	3.0 - 5.0

4	MALE BACK SEAL	1	RUST RED
3	MALE REAR COVER	1	BLACK
2	MALE FRONT COVER	1	GREEN
1	MALE HOUSING	1	GREEN
No.	DESCRIPTION	QTY	COLOUR
BILL OF MATERIAL			




NOTES:

1. REFERENCE SHEET 1 FOR UNSPECIFIED NOTES AND DIMENSIONS
2. MX150 BLADE TERMINALS PER SD-33000-001 TO BE USED WITH THIS ASSEMBLY IN CAVITIES B, C, E AND F, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 1.5mm TO 2.7mm
3. MX150L BLADE TERMINALS PER SD-19431-00* TO BE USED WITH THIS ASSEMBLY IN CAVITIES A, D AND G, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 3.0mm TO 5.0mm
4. MATES WITH: SRC 48+8ADG POWER RECEPTACLE HOUSING ASSEMBLY (GREEN) PART NUMBER 938494808 PER 850840700 PSD

QUALITY SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
= 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0	ADD GREEN OPTIONS EC NO: 114187 DRWN: SMCGREEVY CHK'D: AJOBRIEN APPR: JDWALLACE	2017/04/12 2017/06/30 2017/07/03	GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± ° 4 PLACES ± 3 PLACES ± 2 PLACES ± 0.2 1 PLACE ± 0.5 0 PLACES ± DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DIMENSION UNITS		SCALE		molex®			
MM					1:1							
DRWN BY					DATE		SRC MIXED POWER MALE BLADE HOUSING ASSEMBLY					
AJOBRIEN					2015/08/07							
CHK'D BY					DATE		PRODUCT CUSTOMER DRAWING					
SMCGREEVY					2015/08/14							
APPR BY					DATE		SERIES 93792 MATERIAL NUMBER 938504808 CUSTOMER GENERAL MARKET					
JDWALLACE					2015/09/03							
DRAWING SIZE					THIRD ANGLE PROJECTION		DOCUMENT NUMBER 937921000 DOC TYPE PSD DOC PART 000 SHEET NUMBER 15 OF 16					
A3												



36+12ACEG MAIN HOUSING GREEN



SECTION X-X

ACCEPTABLE CABLE INSULATION Ø RANGES (mm) - NOTES 2 & 3						
CAVITY SET						
G	F	E	D	C	B	A
3.0 - 5.0	1.5 - 2.7	3.0 - 5.0	1.5 - 2.7	3.0 - 5.0	1.5 - 2.7	3.0 - 5.0

4	MALE BACK SEAL	1	RUST RED
3	MALE REAR COVER	1	BLACK
2	MALE FRONT COVER	1	GREEN
1	MALE HOUSING	1	GREEN
No.	DESCRIPTION	QTY	COLOUR
BILL OF MATERIAL			



- NOTES:
1. REFERENCE SHEET 1 FOR UNSPECIFIED NOTES AND DIMENSIONS
 2. MX150 BLADE TERMINALS PER SD-33000-001 TO BE USED WITH THIS ASSEMBLY IN CAVITIES B, D AND F, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 1.5mm TO 2.7mm
 3. MX150L BLADE TERMINALS PER SD-19431-00* TO BE USED WITH THIS ASSEMBLY IN CAVITIES A, C, E AND G, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 3.0mm TO 5.0mm
 4. MATES WITH: SRC 36+12ACEG POWER RECEPTACLE HOUSING ASSEMBLY (GREEN)
PART NUMBER 938493612 PER 850840700 PSD

QUALITY SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
▽_A = 0 ▽_F = 0 ▽_E = 0 ▼ = 0 ▽_C = 0 ⊠ = 0 ■ = 0 ▽_D = 0	ADD GREEN OPTIONS	EC NO: 114187 DRWN: SMCGREEVY CHK'D: AJOBRIEN APPR: JDWALLACE	2017/04/12 2017/06/30 2017/07/03	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex[®]							
						MM		1:1									
						DRWN BY		DATE		SRC MIXED POWER MALE BLADE HOUSING ASSEMBLY							
						AJOBRIEN		2015/08/07									
						CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING							
						SMCGREEVY		2015/08/14									
						APPR BY		DATE		SERIES 93792				MATERIAL NUMBER 938503612		CUSTOMER GENERAL MARKET	
						JDWALLACE		2015/09/03									
						DRAWING SIZE		THIRD ANGLE PROJECTION		DOCUMENT NUMBER 937921000				DOC TYPE PSD	DOC PART 000	SHEET NUMBER 16 OF 16	
						A3											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				B4		REV											