



Part Number : [643211011](#)
Product Description : .635mm, 1.50mm, 2.80mm, CMC Receptacle, 53 Circuits, Left Wire Output, Black Coding, Mat Sealed
Series Number : [64321](#)
Status : Active
Product Category : [Connector Housings](#)



Documents & Resources

Drawings
[643211011_sd.pdf](#)

3D Models and Design Files
[643211011_stp.zip](#)

Specifications
[AS-64318-002-001.pdf](#)
[AS-64318-002-CH-001.pdf](#)
[AS-64318-002-SP-001.pdf](#)
[AS-98420-001-001.pdf](#)
[AS-98420-001-CH-001.pdf](#)
[AS-98420-001-SP-001.pdf](#)
[AS-64318-002-FR-001.pdf](#)
[AS-98420-001-FR-001.pdf](#)
[PK-98995-001-001.pdf](#)
[PS-64321-001-001.pdf](#)
[PS-64321-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2024)6225-DC (07 Nov 2024)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	64321
Description	.635mm, 1.50mm, 2.80mm, CMC Receptacle, 53 Circuits, Left Wire Output, Black Coding, Mat Sealed
Application	Automotive, Power, Wire-to-Board
Comments	Current tested on a fully loaded connector, current for temperature increase of 40°C; Current max = 21.0A for 2.80mm Terminal (5.00mm ² wire), 12.0A for 1.50mm Terminal (2.00mm ² wire), 2.5A for 0.635mm Terminal (0.75mm ² wire)
More Detailed Tech Information	Sealed, high-density, power, modular connecting system for Power Train and Body Electronics applications in cars, trucks, busses
Product Name	CMC
UPC	883906135164

Physical

Circuits Detail	5x 2.8mm, 8 x 1.5mm, 40 x 0.635mm terminals
Circuits (maximum)	53
Color - Resin	Black

Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	50.880/g
Number of Rows	5
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	2.54mm, 3.50mm, 7.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Use with Part(s)

Description	Part Number
Wire Cap for CMC Mat Sealed Receptacle, 53 Circuits	<u>643211101</u>
CMC 0.635mm Blind Cavity Plug	<u>643251010</u>
CMC 1.50mm Blind Cavity Plug	<u>643251023</u>
CMC 2.80mm Blind Cavity Plug	<u>643251091</u>
0.635mm CMC CP Female Terminals	<u>64322</u>
1.50mm CMC CP Female Terminals	<u>64323</u>

Application Tooling

Global

Description	Part Number
Continuity Test Pen Assembly	<u>638121100</u>
Unlocking Tool for CMC and CMX Receptacle Connector	<u>638241200</u>

